

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192030149](#)  
**Status:** **Active**  
**Description:** RING/HI-TEMP/VERSAKRIMP (BB-T-337-06)

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-19902-013-001 (PDF)</a>
<a href="#">Product Specification PS-19902-011-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

UL E32244

**General**

Product Family	Ring and Spade Terminals
Series	<a href="#">19203</a>
Crimp Quality Equipment	Yes
UPC	800755059656

**Physical**

Net Weight 1.373/g

**Material Info**

Engineering Number BB-T-337-06

**Reference - Drawing Numbers**

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	192030148-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19203](#) Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm <sup>2</sup> - 0.5mm <sup>2</sup> Crimp Head for the AT-200 Pneumatic Hand Tool	<a href="#">640030100</a>
ServiceGrade Hand Crimp Tool - Ratchet	<a href="#">640070100</a>
	<a href="#">640160038</a>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19203-0149](#)