

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0192030379**
Status: **Active**
Overview: Standard Quick-Disconnect Terminals
Description: Krimptite Quick Disconnect, Female, Steel, 483°C (900° F), 10-12 AWG, Tab 6.35mm

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Quick Disconnects
Series 19203
Crimp Quality Equipment Yes
Insulated No
Overview Standard Quick-Disconnect Terminals
Product Name Krimptite
Type Quick Disconnect
UPC 822348424689

Physical

Barrel Type Closed
Gender Female
Glow-Wire Capable No
Insulation None
Lock to Mating Part None
Material - Metal Steel
Material - Plating Mating Nickel
Material - Plating Termination Nickel
Net Weight 0.670/g
Orientation Straight
Packaging Type Bag
Tab Thickness 0.80mm
Tab Width 7.70mm
Temperature Range - Operating 483°C
Wire Size AWG 10, 12

Electrical

Voltage - Maximum N/A

Material Info

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
Sales Drawing SD-19203-025



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

19203 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Tool for High Temperature Female Quick Disconnects	640031500

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19203-0379](#)