

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192210417](#)
Status: **Active**
Overview: Battery Cable Lugs
Description: Compression Style Ring Tongue Terminal for 6 AWG Wire, Stud Size 1/2" (M12), Unplated, Extra Wide Pad

Documents:

Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
Product Specification PS-19901-017-001 (PDF)	Product Specification PS-19902-017-001 (PDF)
Product Specification PS-19902-011-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	19221
Comments	Heavy Duty
Crimp Quality Equipment	Yes
Overview	Battery Cable Lugs
Product Name	Battery Cable Lug
Type	Ring
UPC	800753065017

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Unplated
Net Weight	9.779/g
Packaging Type	Bag
Stud Size	1/2" (M12)
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	N/A
Wire Size AWG	6
Wire Size mm ²	10.50-16.80

Material Info

Engineering Number	BCL-612-XWP
--------------------	-------------

Reference - Drawing Numbers

Product Specification	PS-19901-017-001, PS-19902-011-001, PS-19902-013-001, PS-19902-017-001
Sales Drawing	SD-19221-001



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Reviewed

Search Parts in this Series

[19221 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

Hand Crimp Tool for Eyelet Style Copper Lug Terminals 8-4/0 AWG	192840034
---	---------------------------

Manual Putt Pump Hydraulic System, Die set required	192860117
---	---------------------------

Die Set (large) for the HHLS Hydraulic Crimper	192900004
--	---------------------------

Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	192940008
--	---------------------------

Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	192940008
--	---------------------------

Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	192940008
--	---------------------------

Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	192940008
--	---------------------------

Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	192940008
--	---------------------------

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19221-0417](#)