

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192840034](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Hand Crimp Tool for Eyelet Style Copper Lug Terminals 8-4/0 AWG

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Comments	"bolt cutter". Type: E-406
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	800755087994
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight 1852.000/g

Material Info

Engineering Number E-406

Reference - Drawing Numbers

Application Tooling Documents
ATS-192840034-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Not Relevant

Not Contained

Search Parts in this Series

[207129 Series](#)

Application Tooling

Description

FAQ

Product #

Compression [192210223](#)

Style Ring Tongue Terminal for 8 AWG

Wire, Stud Size 10 (M5), Plated,

Compression [192210224](#)

Style Ring Tongue Terminal for 8 AWG

Wire, Stud Size 1/4" (M6), Plated

Compression [192210225](#)

Style Ring Tongue Terminal for 8 AWG

Wire, Stud Size 5/16" (M8), Plated

Compression [192210226](#)

Style Ring Tongue Terminal for 8 AWG

Wire, Stud Size

3/8" (M9), Plated, Wide Pad Compression	<u>192210227</u>
Style Ring Tongue Terminal for 6 AWG Wire, Stud Size 1/4" (M6), Plated, Wide Pad Compression	<u>192210228</u>
Style Ring Tongue Terminal for 6 AWG Wire, Stud Size 5/16" (M8), Plated, Wide Pad Compression	<u>192210229</u>
Style Ring Tongue Terminal for 6 AWG Wire, Stud Size 3/8" (M9), Plated, Wide Pad Compression	<u>192210230</u>
Style Ring Tongue Terminal for 4 AWG Wire, Stud Size 1/4" (M6), Tin Plated Compression	<u>192210231</u>
Style Ring Tongue Terminal for 4 AWG Wire, Stud Size 5/16" (M8), Tin Plated Compression	<u>192210232</u>
Style Ring Tongue Terminal for 4 AWG Wire, Stud Size 3/8" (M9), Tin Plated Compression	<u>192210233</u>
Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 5/16" (M8), Tin Plated Compression	<u>192210234</u>
Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 1/4" (M6), Plated Compression	<u>192210235</u>
Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 3/8" (M9), Tin Plated Compression	<u>192210237</u>
Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 5/16" (M8), Tin Plated Compression	<u>192210238</u>
Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 3/8" (M9), Tin Plated	

Compression Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 1/2" (M12), Tin Plated, Wide Pad	<u>192210239</u>
Compression Style Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 5/16" (M8), Plated	<u>192210240</u>
Compression Style Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 3/8" (M9), Plated	<u>192210241</u>
Compression Style Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 1/2" (M12), Plated	<u>192210242</u>
Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 5/16" (M8), Plated	<u>192210243</u>
Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 3/8" (M9), Plated	<u>192210244</u>
Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 1/2" (M12), Plated	<u>192210245</u>
Compression Style Ring Tongue Terminal for 3/0 AWG Wire, Stud Size 5/16" (M8), Plated	<u>192210246</u>
Compression Style Ring Tongue Terminal for 3/0 AWG Wire, Stud Size 3/8" (M9), Plated	<u>192210247</u>
Compression Style Ring Tongue Terminal for 3/0 AWG Wire, Stud Size 1/2" (M12), Plated	<u>192210248</u>
Compression Style Ring Tongue Terminal for 4/0 AWG Wire, Stud Size 3/8" (M9),	<u>192210250</u>

Plated, Barrel Length 19.05mm Compression	<u>192210251</u>
Style Ring Tongue Terminal for 4/0 AWG Wire, Stud Size 1/2" (M12), Plated, Barrel Length 19.05mm Compression	<u>192210377</u>
Style Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 3/8" (M9), Unplated Compression	<u>192210378</u>
Style Ring Tongue Terminal for 1 AWG Cable, Stud Size 3/8" (M9), Unplated Compression	<u>192210379</u>
Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 3/8" (M9), Unplated Compression	<u>192210380</u>
Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 3/8" (M9), Unplated Compression	<u>192210381</u>
Style Ring Tongue Terminal for 3/0 AWG Wire, Stud Size 3/8" (M9), Unplated Compression	<u>192210382</u>
Style Ring Tongue Terminal for 4/0 AWG Cable, Stud Size 3/8" (M9), Unplated, Barrel Length 19.05mm Compression	<u>192210383</u>
Style Ring Tongue Terminal for 4 AWG Wire, Stud Size 3/8" (M9), Unplated Compression	<u>192210384</u>
Style Ring Tongue Terminal for 6 AWG Wire, Stud Size 3/8" (M9), Unplated, Wide Pad Compression	<u>192210393</u>
Style Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 1/2" (M12), Unplated Compression	<u>192210394</u>
Style Ring Tongue Terminal for 1/0 AWG Wire, Stud	

Size 5/16" (M8), Unplated Compression	<u>192210395</u>
Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 1/2" (M12), Unplated, Wide Pad	
Compression	<u>192210396</u>
Style Ring Tongue Terminal for 1 AWG Wire, Stud Size 5/16" (M8), Unplated	
Compression	<u>192210397</u>
Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 1/2" (M12), Unplated	
Compression	<u>192210398</u>
Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 5/16" (M8), Unplated	
Compression	<u>192210399</u>
Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 1/2" (M12), Unplated, Wide Pad	
Compression	<u>192210400</u>
Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 5/16" (M8), Unplated	
Compression	<u>192210401</u>
Style Ring Tongue Terminal for 3/0 AWG Wire, Stud Size 1/2" (M12), Unplated	
Compression	<u>192210402</u>
Style Ring Tongue Terminal for 3/0 AWG Wire, Stud Size 5/16" (M8), Unplated	
Compression	<u>192210403</u>
Style Ring Tongue Terminal for 4/0 AWG Wire, Stud Size 1/2" (M12), Unplated, Barrel Length 19.05mm	
Compression	<u>192210404</u>
Style Ring Tongue Terminal for 4 AWG Wire, Stud Size 1/4" (M6), Unplated	
Compression	<u>192210405</u>
Style Ring Tongue Terminal for 4 AWG Wire, Stud Size 5/16" (M8), Unplated	

Compression	<u>192210406</u>
Style Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size	
1/4" (M6), Unplated,	
Wide Pad	
Compression	<u>192210407</u>
Style Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size	
5/16" (M8), Unplated,	
Wide Pad	
Compression	<u>192210408</u>
Style Ring tongue	
Terminal for 8 AWG	
Wire, Stud Size 10	
(M5), Unplated	
Compression	<u>192210409</u>
Style Ring Tongue	
Terminal for 8 AWG	
Wire, Stud Size	
1/4" (M6), Unplated	
Compression	<u>192210410</u>
Style Ring Tongue	
Terminal for 8 AWG	
Wire, Stud Size	
3/8" (M9), Unplated,	
Wide Pad	
Compression	<u>192210411</u>
Style Ring Tongue	
Terminal for 8 AWG	
Wire, Stud Size	
5/16" (M8), Unplated	
Compression Ring	<u>192210412</u>
Tongue Terminal	
for 4/0 AWG Wire,	
Stud Size 5/16" (M8),	
Plated, Barrel Length	
19.05mm	
Compression	<u>192210413</u>
Style Ring Tongue	
Terminal for 4/0	
AWG Wire, Stud	
Size 5/16" (M8),	
Unplated, Barrel	
Length 19.05mm	
Compression	<u>192210414</u>
Style Ring Tongue	
Terminal for 8 AWG	
Wire, Stud Size	
1/2" (M12), Plated,	
Extra Wide Pad	
Compression	<u>192210415</u>
Style Ring Tongue	
Terminal for 8 AWG	
Wire, Stud Size	
1/2" (M12), Unplated,	
Extra Wide Pad	
Compression	<u>192210416</u>
Style Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size	
1/2" (M12), Plated,	
Extra Wide Pad	

Compression	<u>192210417</u>
Style Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size	
1/2" (M12), Unplated,	
Extra Wide Pad	
Compression	<u>192210418</u>
Style Ring Tongue	
Terminal for 2 AWG	
Wire, Stud Size	
1/4" (M6), Tin Plated	
Compression	<u>192210419</u>
Style Ring Tongue	
Terminal for 2 AWG	
Wire, Stud Size	
1/4" (M6), Unplated	
Compression	<u>192210420</u>
Style Ring Tongue	
Terminal for 1 AWG	
Wire, Stud Size	
1/4" (M6), Tin Plated	
Compression	<u>192210421</u>
Style Ring Tongue	
Terminal for 1 AWG	
Wire, Stud Size	
1/4" (M6), Unplated	
Compression	<u>192210422</u>
Style Ring Tongue	
Terminal for 1/0	
AWG Wire, Stud	
Size 1/4" (M6),	
Plated	
Compression	<u>192210423</u>
Style Ring Tongue	
Terminal for 1/0	
AWG Wire, Stud	
Size 1/4" (M6),	
Unplated	
Compression	<u>192210424</u>
Style Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size 10	
(M5), Plated	
Compression	<u>192210425</u>
Style Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size 10	
(M5), Unplated	
Compression	<u>192210451</u>
Style Ring Tongue	
Terminal for 4 AWG	
Wire, Stud Size 10	
(M5), Unplated	
Compression	<u>192210452</u>
Style Ring Tongue	
Terminal for 4 AWG	
Wire, Stud Size 10	
(M5), Tin Plated	
Compression	<u>192210453</u>
Style Ring Tongue	
Terminal for 4 AWG	
Wire, Stud Size	
1/2" (M12), Unplated	
Compression	<u>192210454</u>
Style Ring Tongue	

Terminal for 4 AWG
Wire, Stud Size
1/2" (M12), Tin
Plated
Compression 192210456
Style Ring Tongue
Terminal for 4 AWG
Wire, Stud Size
3/8" (M9), Tin Plated,
Wide Pad
Compression 192210458
Style Ring Tongue
Terminal for 4 AWG
Wire, Stud Size
3/8" (M9), Unplated,
Wide Pad
Compression 192210459
Style Ring Tongue
Terminal for 4 AWG
Wire, Stud Size
3/8" (M9), Unplated,
Extra Wide Pad
Compression 192210460
Style Ring Tongue
Terminal for 4 AWG
Wire, Stud Size
5/16" (M8), Tin
Plated, Wide Pad
Compression 192210461
Style Ring Tongue
Terminal for 4 AWG
Wire, Stud Size
5/16" (M8), Unplated,
Wide Pad
Compression 192210478
Style Ring Tongue
Terminal for 3/0
AWG Wire, Stud
Size 1/4" (M6),
Unplated
Compression 192210481
Style Ring Tongue
Terminal for 8 AWG
Wire, Stud Size
3/8" (M9), Unplated,
Extra Wide Pad
Compression 192210482
Style Ring Tongue
Terminal for 8 AWG
Wire, Stud Size
5/16" (M8), Unplated,
Wide Pad
Compression 192210483
Style Ring Tongue
Terminal for 8 AWG
Wire, Stud Size
5/16" (M8), Plated,
Wide Pad
Compression 192210484
Style Ring Tongue
Terminal for 8 AWG
Wire, Stud Size
3/8" (M9), Plated,
Extra Wide Pad

Compression	<u>192210492</u>
Style Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size	
5/16" (M8), Plated	
Compression	<u>192210493</u>
Style Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size	
5/16" (M8), Unplated	
Compression	<u>192210494</u>
Style Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size	
1/4" (M6), Unplated	
Compression	<u>192210495</u>
Style Ring Tongue	
Terminal for 6 AWG	
Wire, Stud Size	
1/4" (M6), Plated	
Compression	<u>192210570</u>
Style Ring Tongue	
Terminal for 3/0	
AWG Wire, Stud	
Size 1/4" (M6),	
Plated	

This document was generated on 10/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19284-0034](#)