

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192880004](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General


Product Family	Application Tooling
Series	207126
Comments	The Crimp Tape Module 640162000 is a base unit that will work like an applicator in a Molex TM-3000 638017200 , 638017300 industry standard crimp press or the Molex TM-4000 638017600 industry standard crimp press. The Crimp Tape Module will accept all ATP-301 and ATP-201 style crimp dies. This Crimp Tape Module will allow customers to process most of Molex's Mylar Tape product from 2 AWG uninsulated and 4 AWG insulated products and up. The Crimp Tape Module will NOT work in any other industry standard crimp press or wire process machine. These ATP-301 style die sets can be used in the older style suitcase presses.
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	ETC
Tool Type	Crimp Module
UPC	800753108622
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number ATP-A-510

Reference - Drawing Numbers

Application Tooling Documents
[192880004-001](#), [ATS-TOOLING-ID-ATP-0](#),
[TM-192280498-001](#), [TM-192280498SP-001](#),
[TM-640160065-001](#), [TM-640160065CN-001](#),
[TM-640160065DE-001](#), [TM-640160065FR-001](#),
[TM-640160065IT-001](#), [TM-640160065JP-001](#),
[TM-640160065KR-001](#), [TM-640160065MY-001](#),
[TM-640160065PL-001](#), [TM-640160065RU-001](#),
[TM-640160065SK-001](#), [TM-640160065SP-001](#),



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[207126 Series](#)

Use With

Molex Crimp Tape Module [640162000](#) used with Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex ATP-301 Press: [192280030](#) and Molex ATP-101 style presses.

Application Tooling | [FAQ](#)

Description

Product #

InsulKrimp Quick [190230006](#)

Disconnect,
Male, for 18-22
(0.80-0.35mm²) Wire,
Mylar Tape, Tab 6.35
x 0.81mm

Avikrimp Quick [190250003](#)

Disconnect,
Male, for 18-22
(0.80-0.35mm²) Wire,
Mylar Tape, Tab 4.75
x 0.51mm

Avikrimp Quick [190250004](#)

Disconnect,
Male, for 18-22

TM-640160065TH-001, TM-640160065TW-001,
TM-640160065VN-001

(0.80-0.35mm²) Wire,
Mylar Tape, Tab 6.35
x 0.81mm
Avikrimp Snap Plug, [190350002](#)
for 18-22 AWG
Wire, Mylar Tape,
24.08mm Length
Avikrimp Snap Plug, [190350004](#)
for 18-22 AWG
Wire, Mylar Tape,
22.55mm Length
Avikrimp Snap Plug, [190360002](#)
for 18-22 AWG
Wire, Mylar Tape,
24.31mm Length
Avikrimp Snap Plug, [190360005](#)
for 18-22 AWG
Wire, Mylar Tape,
22.78mm Length

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19288-0004](#)