

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192880233](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207126</a>
Comments	The Crimp Tape Module <a href="#">640162000</a> is a base unit that will work like an applicator in a Molex TM-3000 <a href="#">638017200</a> , <a href="#">638017300</a> industry standard crimp press or the Molex TM-4000 <a href="#">638017600</a> industry standard crimp press. The Crimp Tape Module will accept all ATP-301 and ATP-201 style crimp dies. This Crimp Tape Module will allow customers to process most of Molex's Mylar Tape product from 2 AWG uninsulated and 4 AWG insulated products and up. The Crimp Tape Module will NOT work in any other industry standard crimp press or wire process machine. These ATP-301 style die sets can be used in the older style suitcase presses.
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	ETC
Tool Type	Crimp Module
UPC	800753110908
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Material Info**

Engineering Number ATP-M-675-CC

**Reference - Drawing Numbers**

Application Tooling Documents  
[192880233-001](#), [ATS-TOOLING-ID-ATP-0](#),  
[TM-192280498-001](#), [TM-192280498SP-001](#),  
[TM-640160065-001](#), [TM-640160065CN-001](#),  
[TM-640160065DE-001](#), [TM-640160065FR-001](#),  
[TM-640160065IT-001](#), [TM-640160065JP-001](#),  
[TM-640160065KR-001](#), [TM-640160065MY-001](#),  
[TM-640160065PL-001](#), [TM-640160065RU-001](#),  
[TM-640160065SK-001](#), [TM-640160065SP-001](#),



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[207126 Series](#)

**Use With**

Molex Crimp Tape Module [640162000](#) used with Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex ATP-301 Press: [192280030](#) and Molex ATP-101 style presses.

**Application Tooling** | **FAQ**

**Description** | **Product #**

InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm<sup>2</sup>), Mylar Tape, Tab 4.75 x 0.51mm, Yellow [190030067](#)

InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm<sup>2</sup>), Mylar Tape, Tab 4.75 x 0.81mm, Dark Yellow [190030070](#)

InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm<sup>2</sup>), Mylar Tape, Tab 4.75 x 0.81mm, Dark Yellow [190030073](#)

InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm<sup>2</sup>), Mylar Tape, Tab 4.75 x 0.81mm, Dark Yellow [190030073](#)

InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm<sup>2</sup>), Mylar Tape, Tab 4.75 x 0.81mm, Dark Yellow [190030073](#)

InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm<sup>2</sup>), Mylar Tape, Tab 4.75 x 0.81mm, Dark Yellow [190030073](#)

InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm<sup>2</sup>), Mylar Tape, Tab 4.75 x 0.81mm, Dark Yellow [190030073](#)

InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm<sup>2</sup>), Mylar Tape, Tab 4.75 x 0.81mm, Dark Yellow [190030073](#)

InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm<sup>2</sup>), Mylar Tape, Tab 4.75 x 0.81mm, Dark Yellow [190030073](#)

InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm<sup>2</sup>), Mylar Tape, Tab 4.75 x 0.81mm, Dark Yellow [190030073](#)

InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm<sup>2</sup>), Mylar Tape, Tab 4.75 x 0.81mm, Dark Yellow [190030073](#)

InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm<sup>2</sup>), Mylar Tape, Tab 4.75 x 0.81mm, Dark Yellow [190030073](#)

InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm<sup>2</sup>), Mylar Tape, Tab 4.75 x 0.81mm, Dark Yellow [190030073](#)

InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm<sup>2</sup>), Mylar Tape, Tab 4.75 x 0.81mm, Dark Yellow [190030073](#)

TM-640160065TH-001, TM-640160065TW-001,  
TM-640160065VN-001

Female, for 24-26  
(0.20-0.12mm<sup>2</sup>),  
Mylar Tape, Tab 6.35  
x 0.81mm, Yellow

This document was generated on 07/31/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19288-0233](#)