

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192890007](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Die Set (large) for the HHLS Hydraulic Crimper

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General


Product Family	Application Tooling
Series	207125
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	ETC
Tool Type	Crimp Module
UPC	800753111639
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number HHL-F-730

Reference - Drawing Numbers

Application Tooling Documents
 ATS-192890007-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[207125 Series](#)

Use With

Molex HHLS Air Powered Hydraulic Crimper 12 Ton [192860058](#) , Manual Putt Pump Hydraulic System [192860117](#) , Electric Powered Hydraulic System [192861300](#)

Application Tooling

FAQ

Description	Product #
NylaKrimp Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud Size 1/2" (M12)	190670076
NylaKrimp Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud Size 1/4" (M6)	190670077
NylaKrimp Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud Size 3/8" (M9)	190670078

NylaKrimp Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud Size 5/16" (M8)	<u>190670079</u>
NylaKrimp Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud Size 7/16" (M11)	<u>190670080</u>
NylaKrimp Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud Size 10 (M5)	<u>190670081</u>
NylaKrimp Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud Size 1/4" (M6)	<u>190670082</u>
NylaKrimp Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud Size 5/16" (M8)	<u>190670084</u>
NylaKrimp Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud Size 1/2" (M12)	<u>190670085</u>
NylaKrimp Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud Size 5/8" (M16)	<u>190670087</u>
NylaKrimp Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud Size 3/4" (M18)	<u>190670088</u>
InsulKrimp Ring Tongue Terminal for 4 AWG Wire	<u>190710231</u>
InsulKrimp Ring Tongue Terminal for 4 AWG Wire	<u>190710234</u>
InsulKrimp Ring Tongue Terminal for 4 AWG Wire	<u>190710237</u>
InsulKrimp Ring Tongue Terminal for 4 AWG Wire	<u>190710240</u>
InsulKrimp Ring Tongue Terminal for 4 AWG Wire	<u>190710243</u>
InsulKrimp Ring Tongue Terminal for 4 AWG Wire	<u>190710250</u>
InsulKrimp Ring Tongue Terminal for 4 AWG Wire	<u>190710253</u>
InsulKrimp Butt Splice for 4 AWG Wire	<u>191540048</u>

NylaKrimp Butt
Splice for 4 AWG
Wire

192020056

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19289-0007](#)