

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0193230001](#)
Status: **Active**
Overview:
Description: VersaKrimp Metric Ring Terminal for M2.5 Stud Size (#4), Un-insulated, Bag

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
 Series [19323](#)
 Crimp Quality Equipment Yes
 Overview [metric_ring_terminals](#)
 Product Name VersaKrimp
 Type Ring
 UPC 887191289151

Physical

Barrel Type Closed - Brazed
 Insulation None
 Material - Metal Copper Alloy
 Material - Plating Mating Tin
 Net Weight 0.465/g
 Packaging Type Bag
 Stud Size M2.5
 Wire Size AWG N/A
 Wire Size mm² 0.50-1.00

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number AA1-332-M2,5

Reference - Drawing Numbers

Sales Drawing SD-19323-001-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2021)4569-DC (8
 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19323](#) Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm ² - 0.5mm ² Crimp Head for the AT-200 Pneumatic Hand Tool	640030100
ServiceGrade Hand Crimp Tool - Ratchet	640070100
	640160038

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19323-0001](#)