

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0193240014](#)
Status: **Active**
Overview: Metric Ring Terminals
Description: Avikrimp Metric Ring Terminal for Stud Size 1/4" (M6), Insulated Barrel

Documents:

[3D Model \(PDF\)](#) [Drawing \(PDF\)](#)
[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
Series [19324](#)
Crimp Quality Equipment Yes
Overview [Metric Ring Terminals](#)
Product Name Avikrimp
Type Ring
UPC 887191290140

Physical

Barrel Type Closed - Brazed
Flammability 94V-2
Insulation Nylon (PA)
Material - Metal Copper Alloy
Material - Plating Mating Tin
Net Weight 2.828/g
Packaging Type Bag
Stud Size M8
Wire Size AWG N/A
Wire Size mm² 2.50-6.00

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number C6-830-M6

Reference - Drawing Numbers

Sales Drawing SD-19324-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19324 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm ² (Rings, Spades, Hooks, Block Spades and Flanged Spades)	640010100
Crimp Head for the AT-200 Pneumatic Hand Tool	640050100

ServiceGrade Hand 640160036
Crimp Tool for Field
Repair only, for
production use our
PremiumGrade Tool

This document was generated on 11/18/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19324-0014](#)