

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0393740902](#)  
**Status:** **Active**  
**Overview:** Eurostyle Terminal Blocks  
**Description:** 7.50mm Beau Eurostyle Pluggable PCB Terminal Block, 270° Wire Entry, 2 Circuits

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E48521

**General**

Product Family	Terminal Blocks
Series	<a href="#">39374</a>
Application	N/A
Component Type	Plug
Overview	<a href="#">Eurostyle Terminal Blocks</a>
Product Name	Eurostyle Pluggable
Type	Euro Block
UPC	822348047352

**Physical**

Circuits (Loaded)	2
Entry Angle	270
Flammability	94V-0
Lock to Mating Part	None
Number of Rows	1
Orientation	Vertical
PCB Retention	N/A
Panel Mount	No
Pitch - Mating Interface	7.50mm
Pitch - Termination Interface	7.50mm
Polarized to Mating Part	Yes
Stackable	Yes
Temperature Range - Operating	110°C
Wire Size AWG	12, 14, 16, 18, 20, 22, 24, 26, 28, 30
Wire Size mm <sup>2</sup>	0.05-2.50

**Electrical**


Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

**Material Info**

Engineering Number MX-CVF020R3-0N

**Reference - Drawing Numbers**

Sales Drawing SD-39374-002



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[39374](#) Series

**Mates With**

[39372](#) , [39373](#) Headers

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39374-0902](#)