

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0395021015](#)  
**Status:** **Active**  
**Overview:** Eurostyle Terminal Blocks  
**Description:** 3.50mm Pitch Eurostyle Horizontal PCB Header, 15 Circuits

**Documents:**

|                                |                                                              |
|--------------------------------|--------------------------------------------------------------|
| <a href="#">3D Model</a>       | <a href="#">Product Specification PS-39500-001-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>  | <a href="#">RoHS Certificate of Compliance (PDF)</a>         |
| <a href="#">3D Model (PDF)</a> |                                                              |

**Agency Certification**

UL E48521

**General**

|                |                                           |
|----------------|-------------------------------------------|
| Product Family | Terminal Blocks                           |
| Series         | <a href="#">39502</a>                     |
| Application    | N/A                                       |
| Component Type | PCB Header                                |
| Overview       | <a href="#">Eurostyle Terminal Blocks</a> |
| Product Name   | ESE, Eurostyle Pluggable                  |
| Type           | Euro Block                                |
| UPC            | 822350435086                              |

**Physical**

|                               |                |
|-------------------------------|----------------|
| Circuits (Loaded)             | 15             |
| Entry Angle                   | N/A            |
| Lock to Mating Part           | None           |
| Number of Rows                | 1              |
| Orientation                   | Horizontal     |
| PC Tail Length                | 3.50mm         |
| PCB Thickness - Recommended   | 2.50mm         |
| Panel Mount                   | No             |
| Pitch - Mating Interface      | 3.50mm         |
| Pitch - Termination Interface | 3.50mm         |
| Polarized to Mating Part      | Yes            |
| Shrouded                      | Fully          |
| Stackable                     | No             |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size AWG                 | N/A            |


**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 8.0A |
| Voltage - Maximum             | 300V |

**Material Info**

**Reference - Drawing Numbers**

|                       |                                |
|-----------------------|--------------------------------|
| Product Specification | PS-39500-001-001               |
| Sales Drawing         | SD-39501-002, SD-39502-001-001 |



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[39502](#) Series

**Mates With**

Most 3.50mm Pitch Industry Standard Plugs, [39500](#) Horizontal Plug, [39503](#) Vertical Plug

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39502-1015](#)