

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0395285028](#)
Status: **Active**
Overview:
Description: 5.00mm Pitch Eurostyle Horizontal PCB Dual Level Header, Open Ends, Green Housing, 28 Circuits

Agency Certification

UL E48521

General

Product Family Terminal Blocks
 Series [39528](#)
 Application N/A
 Component Type PCB Header
 Overview eurostyle_terminal_blocks
 Product Name ESE, Eurostyle Pluggable
 Type Euro Block
 UPC 822350527088

Physical

Circuits (Loaded) 28
 Entry Angle N/A
 Lock to Mating Part Yes
 Number of Rows 2
 Orientation Horizontal
 PC Tail Length 5.00mm
 PCB Thickness - Recommended 3.05mm
 Panel Mount No
 Pitch - Mating Interface 5.00mm
 Pitch - Termination Interface 5.00mm
 Polarized to Mating Part Yes
 Shrouded Open Ends
 Stackable Yes
 Surface Mount Compatible (SMC) N/A
 Temperature Range - Operating -40° to +105°C
 Wire Size AWG N/A

Electrical

Current - Maximum per Contact 15.0A
 Voltage - Maximum 300V

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Product Specification PS-39500-001-001
 Sales Drawing SD-39528-001-001

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[39528](#) Series

Mates With

[39520](#) Horizontal Plug, [39523](#) Vertical Plug,
 Most 5.00mm Pitch Industry Standard Plugs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39528-5028](#)