

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0398801208](#)
Status: **Active**
Overview:
Description: 5.08mm Pitch Horizontal Fixed Mount PCB Terminal Block, 8 Circuits

Agency Certification

CSA	LR25562
UL	E48521

General

Product Family	Terminal Blocks
Series	39880
Application	N/A
Component Type	One Piece
Overview	eurostyle_terminal_blocks
Product Name	Eurostyle Fixed Mount
Type	Euro Block
UPC	800756723839

Physical

Circuits (Loaded)	8
Circuits (maximum)	8
Entry Angle	90° Angle
Flammability	94V-0
Lock to Mating Part	None
Number of Rows	1
Orientation	Horizontal
PC Tail Length	3.60mm
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Panel Mount	No
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	12, 14, 16, 18, 20, 22, 24, 26, 28, 30

Electrical

Current - Maximum per Contact	17.5A
Voltage - Maximum	300V

Material Info

Engineering Number	MX-MSM08095-0N
--------------------	----------------

Reference - Drawing Numbers

Sales Drawing	SD-39880-011-001
---------------	------------------

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[39880](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39880-1208](#)