

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0399900312](#)
Status: **Active**
Overview: Eurostyle™ Terminal Blocks
Description: 5.00mm Pitch Beau™ Eurostyle™ Screw Clamp Plug, 12 Circuits

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

UL E48521

General

Product Family Terminal Blocks
 Series [39990](#)
 Application N/A
 Comments Gold plating available
 Component Type Plug
 Overview [Eurostyle™ Terminal Blocks](#)
 Product Name Eurostyle™ Pluggable
 Type Euro Block
 UPC 800753316669

Physical

Circuits (Loaded) 12
 Color - Resin Black
 Entry Angle Horizontal
 Flammability 94V-0
 Lock to Mating Part Yes
 Material - Metal Brass
 Material - Resin Nylon
 Number of Rows 1
 Orientation Vertical
 PCB Retention N/A
 Panel Mount No
 Pitch - Mating Interface 5.00mm
 Pitch - Termination Interface 5.00mm
 Polarized to Mating Part Yes
 Shrouded Fully
 Stackable No
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating 110°C
 Termination Interface: Style Surface Mount
 Wire Size AWG 12, 14, 16, 18, 20, 22, 24

Electrical


Current - Maximum per Contact 10.0A
 Voltage - Maximum 300V

Material Info

Old Part Number 990912

Reference - Drawing Numbers

Sales Drawing SD-39990-001, SD-39990-003



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

Search Parts in this Series

[39990 Series](#)

Mates With

[39990-0412](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39990-0312](#)