

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0417910843](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: [KK 396 Header, Vertical, Friction Lock, 13 Circuits, 0.38µm Gold \(Au\) Selective Plating](#)

Documents:

| | |
|--------------------------------|--|
| 3D Model | Product Specification PS-08-50-001 (PDF) |
| 3D Model (PDF) | Packaging Specification PK-41791-001-001 (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|----------------|---|
| Product Family | PCB Headers |
| Series | 41791 |
| Application | Power, Wire-to-Board |
| Overview | KK Interconnect Solutions |
| Product Name | KK 396 |
| UPC | 822348229321 |

Physical


| | |
|--------------------------------|---------------------------|
| Breakaway | No |
| Circuits (Loaded) | 13 |
| Circuits (maximum) | 13 |
| Color - Resin | Natural |
| Durability (mating cycles max) | 50 |
| Flammability | 94V-0 |
| Glow-Wire Capable | No |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Gold |
| Material - Resin | Polyester |
| Net Weight | 4.849/g |
| Number of Rows | 1 |
| Orientation | Vertical |
| PC Tail Length | 3.56mm |
| PCB Locator | No |
| PCB Retention | None |
| PCB Thickness - Recommended | 1.60mm |
| Packaging Type | Bag |
| Pitch - Mating Interface | 3.96mm |
| Plating min - Mating | 0.381µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | No |
| Shrouded | Partial |
| Stackable | Yes |
| Temperature Range - Operating | See Product Specification |
| Termination Interface: Style | Through Hole |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 7.0A |
| Voltage - Maximum | 250V |

Solder Process Data

| | |
|--|------|
| Duration at Max. Process Temperature (seconds) | 005 |
| Lead-freeProcess Capability | WAVE |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[41791](#) Series

Mates With

[2139](#) KK Crimp Housing, [41695](#) KK Crimp Housing, [6442](#) KK Crimp Housing, [2145](#) PCB Connector, [41815](#) PCB Connector, [3069](#) KK Crimp Housing

| | |
|---|-----|
| Max. Cycles at Max. Process Temperature | 001 |
| Process Temperature max. C | 235 |

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|------------------------------|
| Packaging Specification | PK-41791-001-001 |
| Product Specification | PS-08-50-001 |
| Sales Drawing | SDA-41791-000, SDA-41791-002 |

This document was generated on 12/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[41791-0843](#)