

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0438796038](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: Mini-Fit BMI Header Compliant Pin Interface, Dual Row, Vertical, 24 Circuits, Make First/Break Last, Tin (Sn) over Nickel Plating, Press Fit Tail

Documents:

3D Model	Packaging Specification PK-43879-001-000 (PDF)
3D Model (PDF)	Test Summary TS-43879-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-43879-001-001 (PDF)	

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	43879
Application	Board-to-Board, Power, Wire-to-Board
Comments	Square Pin Compliant Pin
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit BMI
UPC	884982680500

Physical

Breakaway	No
Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	Yes
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Material - Resin	High Temperature Thermoplastic
Net Weight	11.363/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	6.25mm
PCB Locator	No
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole - Compliant Pin



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[43879](#) Series

Mates With

[5557](#) Mini-Fit Jr. Receptacle Housing, [42385](#) Mini-Fit BMI Receptacle Header, Mini-Fit BMI Receptacle Housing [42474](#) , [44516](#)

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V AC (RMS)/DC

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info**Reference - Drawing Numbers**

Packaging Specification	PK-43879-001-000
Product Specification	PS-43879-001-001
Sales Drawing	SD-43879-061-000
Test Summary	TS-43879-001-001

This document was generated on 01/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[43879-6038](#)