

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0441331208**
Status: **Active**
Overview: Micro-Fit Connector System
Description: Micro-Fit BMI Receptacle Housing, Dual Row, Panel Mount, 12 Circuits, Nylon, UL 94V-0, Halogen-Free

Documents:

3D Model (PDF)	Test Summary TS-43045-001-001 (PDF)
3D Model	Test Summary TS-43045-002-001 (PDF)
Drawing (PDF)	Test Summary TS-43045-003-001 (PDF)
Product Specification PS-44300-001-001 (PDF)	Test Summary TS-46235-001-001 (PDF)
Application Specification 443000001-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-44133-002-001 (PDF)	Product Literature (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	<u>44133</u>
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Halogen-Free
Overview	<u>Micro-Fit Connector System</u>
Product Name	Micro-Fit BMI
UPC	883906425548

Physical

Circuits (maximum)	12
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	No
Material - Resin	Nylon
Net Weight	2.327/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	443000001-AS-000
Packaging Specification	PK-44133-002-001
Product Specification	PS-44300-001-001
Sales Drawing	SD-44133-003-001
Test Summary	TS-43045-001-001, TS-43045-002-001, TS-43045-003-001, TS-46235-001-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[44133 Series](#)

Use With

Micro-Fit 3.0 Female Crimp Terminals [43030](#)
, [45773](#)
Micro-Fit RMF Female Crimp
Terminals [46235](#)
Micro-Fit 3.0 Pre-
Crimped Leads [797580002](#) , [797580004](#) ,
[797580010](#) , [797580012](#) , [214760](#) , [214761](#)

This document was generated on 08/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[44133-1208](#)