

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0441930003**
Status: **Active**
Overview: Magnetic and Modular Jacks/Plugs
Description: Modular Jack, Right-Angle, Low Profile, Surface Mount, 8/8, 2 Ports

Documents:

| | |
|--------------------------------|--|
| 3D Model (PDF) | Product Specification PS-43743-0001-001 (PDF) |
| 3D Model | Packaging Specification PK-70873-700-001 (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E107635 |

General

| | |
|---------------------------|---|
| Product Family | Modular Jacks/Plugs |
| Series | 44193 |
| Comments | Flush Solder Tabs |
| Component Type | PCB Jack |
| Magnetic | No |
| Overview | <u>Magnetic and Modular Jacks/Plugs</u> |
| Performance Category | 3 |
| Power over Ethernet (PoE) | N/A |
| Product Name | Modular Jack 8/8, RJ45 |
| UPC | 800754802406 |

Physical

| | |
|--------------------------------|--------------------------------|
| Color - Resin | Black |
| Durability (mating cycles max) | 500 |
| Flammability | 94V-0 |
| Inverted / Top Latch | No |
| Jack Height | 11.80mm |
| Lightpipes/LEDs | None |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 5.175/g |
| Orientation | Right Angle (Side Entry) |
| PCB Retention | Yes |
| Packaging Type | Embossed Tape on Reel |
| Pitch - Mating Interface | 1.02mm |
| Pitch - Termination Interface | 1.27mm |
| Plating min - Mating | 1.270µm |
| Plating min - Termination | 2.540µm |
| Port Configuration | 1x2 |
| Positions / Loaded Contacts | 8/8 |
| Surface Mount Compatible (SMC) | N/A |
| Temperature Range - Operating | -40° to +80°C |
| Termination Interface: Style | Surface Mount |
| Wire/Cable Type | N/A |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 1.5A |
| Shielded | No |
| Voltage - Maximum | 125V |

Solder Process Data



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

44193 Series

Mates With

FCC 68 Plugs

| | |
|--|--------|
| Duration at Max. Process Temperature (seconds) | 030 |
| Lead-freeProcess Capability | REFLOW |
| Max. Cycles at Max. Process Temperature | 001 |
| Process Temperature max. C | 235 |

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|------------------------------------|
| Packaging Specification | PK-70873-700+-001 |
| Product Specification | PS-43743-0001-001 |
| Sales Drawing | SD-44193-001-001, SD-44193-001-002 |

This document was generated on 01/05/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[44193-0003](#)