

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638019100](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: PT-1500 Bench-Top Wire Crimp Pull-Force Tester, Manual Lever-operated for 5.84mm 8-30 AWG

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207124
Comments	See Tooling Specification (PDF) Above
Function	Pull Force
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Crimp Quality Equipment
UPC	884982059566
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number PT-1500

Reference - Drawing Numbers

Application Tooling Documents

TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638019100-001, TM-638019100CN-001, TM-638019100DE-001, TM-638019100FR-001, TM-638019100IT-001, TM-638019100JP-001, TM-638019100KR-001, TM-638019100MY-001, TM-638019100PL-001, TM-638019100RU-001, TM-638019100SK-001, TM-638019100SP-001, TM-638019100TH-001, TM-638019100TW-001, TM-638019100VN-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001,



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[207124 Series](#)

TM-640160065PL-001, TM-640160065RU-001,
TM-640160065SK-001, TM-640160065SP-001,
TM-640160065TH-001, TM-640160065TW-001,
TM-640160065VN-001

This document was generated on 10/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63801-9100](#)