

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0638116100](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** PremiumGrade Hand Crimp Tool for MX150 Female Terminals for 1.00mm<sup>2</sup> and 1.50mm<sup>2</sup> Metric Wires

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207129</a>
Comments	Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	822350665964
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.


**Physical**

Net Weight 428.885/zg

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents  
ATS-6381161HM-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/61/2018 (27 June 2018)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[207129](#) Series

**Use With**

Loose Piece Terminals

**Application Tooling**

**Description**

**FAQ**

**Product #**

MX150 Female Terminal for Mat- Sealed Connectors, Gold Plating, 14 and 16 AWG, Right Reel Payoff [330012003](#)

MX150 Female Terminal for Mat- Sealed Connectors, Gold Plating, 18 and 20 AWG, Right Reel Payoff

[330012004](#)

MX150 Female Terminal for Unsealed Connectors, Gold Plating, 14 and 16 AWG, Right Reel

[330012021](#)

Payoff. Not suitable  
for MX150 Sealed  
Connectors.

MX150 Female 330012022  
Terminal for

Unsealed  
Connectors, Gold  
Plating, 18 and 20  
AWG, Right Reel

Payoff. Not suitable  
for MX150 Sealed  
Connectors.

MX150 Female 330013003  
Terminal for Mat-

Sealed Connectors,  
Gold Plating, 14 and  
16 AWG, Left Reel

Payoff

MX150 Female 330013004  
Terminal for Mat-

Sealed Connectors,  
Gold Plating, 16, 18  
and 20 AWG, Left  
Reel

Payoff

MX150 Female 330013021  
Terminal for

Unsealed  
Connectors, Gold  
Plating, 14 and 16  
AWG, Left Reel

Payoff. Not suitable  
for MX150 Sealed  
Connectors.

MX150 Female 330013022  
Terminal for

Unsealed  
Connectors, Gold  
Plating, 18 and 20  
AWG, Left Reel

Payoff. Not suitable  
for MX150 Sealed  
Connectors.

MX150 Female 330014001  
Terminal for Mat-

Sealed Connectors,  
Silver Plating, 14 and  
16 AWG, Right Reel

Payoff

MX150 Female 330014002  
Terminal for Mat-

Sealed Connectors,  
Silver Plating, 18 and  
20 AWG, Right Reel

Payoff

MX150 Female 330014021  
Terminal for

Unsealed  
Connectors, Silver  
Plating, 14 and 16  
AWG, Right Reel

Payoff. Not suitable  
for MX150 Sealed  
Connectors.

MX150 Female 330014022  
Terminal for

Unsealed  
Connectors, Silver  
Plating, 18 and 20  
AWG, Right Reel  
Payoff. Not suitable  
for MX150 Sealed  
Connectors.

MX150 Female 330015001

Terminal for Mat-  
Sealed Connectors,  
Silver Plating, 14 and  
16 AWG, Left Reel  
Payoff

MX150 Female 330015002

Terminal for Mat-  
Sealed Connectors,  
Silver Plating, 18 and  
20 AWG, Left Reel  
Payoff

MX150 Female 330015021

Terminal for  
Unsealed  
Connectors, Silver  
Plating, 14 and 16  
AWG, Left Reel  
Payoff. Not suitable  
for MX150 Sealed  
Connectors.

MX150 Female 330015022

Terminal for  
Unsealed  
Connectors, Silver  
Plating, 18 and 20  
AWG, Left Reel  
Payoff. Not suitable  
for MX150 Sealed  
Connectors.

MX150 Female 330122001

Terminal for Mat-  
Sealed Connectors,  
Tin Plating, 14 and  
16 AWG, Right Reel  
Payoff

MX150 Female 330122002

Terminal for Mat-  
Sealed Connectors,  
Tin Plating, 18 and  
20 AWG, Right Reel  
Payoff

MX150 Female 330122021

Terminal for  
Unsealed  
Connectors, Tin  
Plating, 14 and 16  
AWG, Right Reel  
Payoff. Not suitable  
for MX150 Sealed  
Connectors.

MX150 Female 330122022

Terminal for  
Unsealed  
Connectors, Tin  
Plating, 18 and 20  
AWG, Right Reel  
Payoff. Not suitable

for MX150 Sealed  
Connectors.

MX150 Female 330123001

Terminal for Mat-  
Sealed Connectors,  
Tin Plating, 14 and  
16 AWG, Left Reel  
Payoff

MX150 Female 330123002

Terminal for Mat-  
Sealed Connectors,  
Tin Plating, 18 and  
20 AWG, Left Reel  
Payoff

MX150 Female 330123021

Terminal for  
Unsealed  
Connectors, Tin  
Plating, 14 and 16  
AWG, Left Reel  
Payoff. Not Suitable  
for MX150 Sealed  
Connectors.

MX150 Female 330123022

Terminal for  
Unsealed  
Connectors, Tin  
Plating, 18 and 20  
AWG, Left Reel  
Payoff. Not Suitable  
for MX150 Sealed  
Connectors.

This document was generated on 10/07/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63811-6100](#)