

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0638192300**
Status: **Active**
Overview: Application Tooling
Description: PremiumGrade Hand Crimp Tool for iGrid Female Terminals, 22-26 AWG and 0.30-0.20mm² Wire

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	<u>207129</u>
Comments	See Tooling Specification (PDF) Above. Type: 4D
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	<u>Application Tooling</u>
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	883906191245
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight 317.100/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents
 ATS-638192300-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

207129 Series

Use With

501647 2.00mm Pitch iGrid Wire-to-Board Crimp Terminal

Application Tooling | **FAQ**

Description	Product #
2.00mm Pitch, iGrid Female Crimp Terminal, Tin (Sn) Plating, 22-26 AWG, Reel	<u>5016471000</u>
2.00mm Pitch, iGrid Female Crimp Terminal, Tin (Sn) Plating, 22-26 AWG, Bag	<u>5016471100</u>
2.00mm Pitch, iGrid Female Crimp Terminal, 0.10µm Gold (Au) Plating, 22-24 AWG, Reel	<u>5030952201</u>

2.00mm Pitch, iGrid Female Crimp Terminal, 0.38µm Gold (Au) Plating, 22-24 AWG, Reel	<u>5030953201</u>
2.00mm Pitch, iGrid Female Crimp Terminal, 0.76µm Gold (Au) Plating, 22-24 AWG, Reel	<u>5030954201</u>

This document was generated on 10/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63819-2300](#)