

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0638193400](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Hand Crimp Tool for CP 2.8 Receptacle 18-20 AWG Type TXL Wire and 0.50-0.75mm<sup>2</sup> Type ID & ID Wire with 2.80mm, CMC Wire Seal Receptacle

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207129</a>
Comments	Field Repair, See Tooling Specification (PDF) Above. Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	883906383831
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Physical**

Net Weight 428.885/zg

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents  
ATS-6381934HM-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/61/2018 (27 June 2018)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[207129](#) Series

**Use With**

Battery Powered Crimping Tool [638160200](#), [638160250](#), Air Powered Crimping Tool [638160100](#)

**Application Tooling**

**Description**

**FAQ**

**Product #**

2.80mm, CMC CP [643241049](#)

Female Terminal, Tin plated, for Tab Dimensions 2.80mm by 0.80mm, Wire Size 0.50-1.00mm<sup>2</sup>

2.80mm, CMC CP [643241149](#)

Female Terminal, Tin plated, Selective 1.27µm Gold in Contact Area, for Tab Dimensions 2.80mm by 0.80mm, Wire Size 0.50-1.00mm<sup>2</sup>

This document was generated on 10/05/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63819-3400](#)