

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0638280200](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Hand Crimp Tool for Micro-Fit 3.0 Female Crimp Terminals, 0.75mm<sup>2</sup> and 18AWG (UL1061) wires

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207129</a>
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	Micro-Fit 3.0
Tool Type	Hand Crimp Tool
UPC	889056667791
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents [ATS-638280200-001](#)



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[207129](#) Series

**Application Tooling** | [FAQ](#)

**Description** | **Product #**

Micro-Fit High-Current RMF Crimp Terminal, Female, 2.540µm Bright Tin Plating, 18 AWG [2039510001](#)

Micro-Fit 3.0 Crimp Terminal, Female, with Tin (Sn) [430300038](#)

Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max

Insulation Outside Diameter, Reel

Micro-Fit 3.0 Crimp Terminal, Female, with 0.38µm

Select Gold (Au) Plated Phosphor Bronze Contact,

18 AWG, .073in / 1.85mm Max

Insulation Outside Diameter, Reel

Micro-Fit 3.0 Crimp Terminal, Female, with 0.38µm

Select Gold (Au) Plated Phosphor Bronze Contact,

18 AWG, .073in / 1.85mm Max

Insulation Outside Diameter, Reel

Micro-Fit 3.0 Crimp Terminal, Female, with 0.38µm

Select Gold (Au) Plated Phosphor Bronze Contact,

18 AWG, .073in / 1.85mm Max

Insulation Outside Diameter, Reel

Micro-Fit 3.0 Crimp Terminal, Female, with 0.38µm

Select Gold (Au) Plated Phosphor Bronze Contact,

18 AWG, .073in / 1.85mm Max

Insulation Outside Diameter, Reel

Micro-Fit 3.0 Crimp Terminal, Female, with 0.38µm

Select Gold (Au) Plated Phosphor Bronze Contact,

18 AWG, .073in / 1.85mm Max

18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel Micro-Fit 3.0	<u>430300040</u>
Crimp Terminal, Female, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel Micro-Fit 3.0 Crimp	<u>430310021</u>
Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel Micro-Fit 3.0	<u>430310022</u>
Crimp Terminal, Male, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel Micro-Fit 3.0	<u>430310023</u>
Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 18 AWG, .073in / 1.85mm Max Insulation Outside Diameter, Reel	

This document was generated on 10/06/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63828-0200](#)