

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638858800](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Mini-Mac Air Feed Mylar Tape Conductor Only Applicator


Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207127
Comments	The Molex Tape Applicator requires an industry standard crimp press with a 4way air like the Molex TM-3000: 638017200 , 638017300 , and the Molex TM-4000: 638017600
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Mini-Mac
Tool Type	Applicator
UPC	884982756946
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers
Application Tooling Documents [ATS-638858800-001](#)



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[207127 Series](#)

Use With

Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling | [FAQ](#)

Description | **Product #**

Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm²) Wire, Mylar Tape, Tab 2.79 x 0.51mm [190160002](#)

Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm²) Wire, Mylar Tape, Tab 2.79 x 0.81mm [190160004](#)

Krimptite Quick Disconnect, Female, for 18-22 (0.80-0.35mm²) Wire, [190160007](#)

Disconnect, Female, for 18-22 (0.80-0.35mm²) Wire,

Disconnect, Female, for 18-22 (0.80-0.35mm²) Wire,

Mylar Tape, Tab 4.75
x 0.81mm
Krimptite Quick 190160008
Disconnect,
Female, for 18-22
(0.80-0.35mm²) Wire,
Mylar Tape, Tab 4.75
x 0.51mm
Krimptite Quick 190160010
Disconnect,
Female, for 18-22
(0.80-0.35mm²) Wire,
Mylar Tape, Tab 6.35
x 0.81mm
Quixon Quick 192730009
Disconnect, Krimptite
Style, Female, Un-
insulated, 18-20
AWG, Mylar Tape

This document was generated on 10/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63885-8800](#)