

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638885000](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Mini-Mac Applicator for KK and Trifurcon, 3.96mm Terminals, 18-24 AWG, check ATS for Wire Insulation Diameter Compatibility

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Mini-Mac
Tool Type	Applicator
UPC	887191272238
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight 4815.002/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents
 ATS-638885000-001, TM-638800000-001, TM-638800000SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001

Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

China RoHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[207127](#) Series

Use With

Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling

FAQ

Description

Product #

KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Brass Tin (Sn)	8500105
KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Phosphor Bronze, Tin (Sn)	8520071
KK Trifurcon Crimp Terminal 6838, 18-20 AWG, Reel, Phosphor Bronze Tin(Sn)	8520112
KK 156 TERMINAL CRIMP 18-24 AWG	8530811
KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Brass, 0.51µm Selective Gold (Au)	8560105
KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Phosphor Bronze,	8580121

0.51µm Selective Gold (Au)	
KK Trifurcon Crimp	<u>8580187</u>
Terminal 6438, 18-20 AWG, Reel, Phosphor Bronze Gold (Au)	
KK 396 Crimp	<u>8650114</u>
Terminal 2478, 18-24 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au)	
3.96mm Pitch	<u>1721601803</u>
EdgeMate Crimp Terminal, Phosphor Bronze, Tin (Sn), Bifurcated, 18-20 AWG, Reel	
3.96mm Pitch	<u>1721601805</u>
EdgeMate Crimp Terminal, Brass, Gold (Au), Bifurcated, 18-20 AWG, Reel	
KK 396 Crimp	<u>39000286</u>
Terminal 2478, 18-24 AWG, Reel, Brass, 0.9µm Pre-Plated Tin (Sn)	
KK 156 TERMINAL CRIMP 18-24 AWG	<u>40011118</u>

This document was generated on 10/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63888-5000](#)