

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638912000](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Mini-Mac Applicator for Mini-Fit Sr. Male and Female Terminals for 14-16 AWG Wire with Insulation Diameter no greater than 3.33mm

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Mini-Mac
Tool Type	Applicator
UPC	800756656052
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight 4939.896/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents
 ATS-638912000-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638000100-001, TM-638000100SP-001

Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

China RoHS

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Not Reviewed

Search Parts in this Series

[207127](#) Series

Use With

Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling

Description

FAQ

Product #

Mini-Fit Sr. Crimp Terminal, Female, 14-16 AWG, Gold (Au)	428150042
Mini-Fit Sr. Crimp Terminal, Female, 14-16 AWG, Silver (Ag)	428150144
Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Gold (Au)	428170042
Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Tin (Sn)	428170141
Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Gold (Au)	428170142
Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Silver (Ag)	428171044
Mini-Fit Sr. Crimp Terminal, Male,	428171144

14-16 AWG, Silver
(Ag)

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63891-2000](#)