

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638951200](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Mini-Mac Applicator for CP2.8 Terminals, 0.50-1.00mm² ID & IR Wire

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|--------------------------------|---|
| Product Family | Application Tooling |
| Series | 207127 |
| Comments | See Tooling Specification (PDF) Above |
| Function | Crimp |
| Geographic Area | Global |
| Level of Automation | Automatic, Semi-Automatic |
| More Detailed Tech Information | applicationtooling@molex.com |
| Overview | Application Tooling |
| Product Name | Mini-Mac |
| Tool Type | Applicator |
| UPC | 883906516833 |
| Warranty Disclaimer | CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified. |

Material Info

Reference - Drawing Numbers
[Application Tooling Documents](#)

ATS-638951200-001, TM-638000100-001,
 TM-638000100SP-001, TM-638800000-001,
 TM-638800000SP-001

Series image - Reference only

EU ELV
Not Reviewed

EU RoHS **China RoHS**
Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

| | |
|-----------------|--------------|
| China ROHS | Not Reviewed |
| ELV | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

Search Parts in this Series

[207127 Series](#)

Use With

Molex TM-3000: [638017200](#) , [638017300](#)
 , Molex TM-4000: [638017600](#) , Molex
 TM-2000: [638008300](#) , [638008400](#) , and
 Most Industry Standard Presses or Wire
 Process Machines

Application Tooling | **FAQ**
Description **Product #**

2.80mm, CMC CP [643241049](#)

Female Terminal,
 Tin plated, for Tab
 Dimensions 2.80mm
 by 0.80mm, Wire
 Size 0.50-1.00mm²

2.80mm, CMC CP [643241149](#)

Female Terminal,
 Tin plated, Selective
 1.27µm Gold in
 Contact Area, for
 Tab Dimensions
 2.80mm by
 0.80mm, Wire Size
 0.50-1.00mm²

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63895-1200](#)