

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0639023900](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: FineAdjust Applicator for Insulation OD 1.40-1.70mm - 18-24 AWG

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	FineAdjust
Tool Type	Applicator
UPC	884982652675
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight 4685.046/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-639023900-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900DE-001, TM-638004900FR-001, TM-638004900IT-001, TM-638004900JP-001, TM-638004900KR-001, TM-638004900MY-001, TM-638004900PL-001, TM-638004900RU-001, TM-638004900SK-001, TM-638004900SP-001, TM-638004900TH-001, TM-638004900TW-001, TM-638004900VN-001



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[207127](#) Series

Use With

Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling

Description

FAQ

Product #

Mini-Fit Jr.	304901002
Grounding Pin, 18-24 AWG, Reel, Phosphor Bronze, Tin or Select Gold (Au)	
Mini-Fit Jr. Crimp Grounding Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 18-24 AWG, Reel	304902002
Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper	39000038

(Cu) Plated Brass,
18-24, 22+22 AWG,
Reel
Mini-Fit Male Crimp 39000040
Terminal, Tin
(Sn) over Copper
(Cu) Plated Brass
Contact, 18-24,
22+22 AWG, Reel
Mini-Fit Female 39000059
Crimp Terminal, Tin
(Sn) over Phosphor
Bronze, 18-24, 22
+22 AWG, Reel
Mini-Fit Male Crimp 39000061
Terminal, Tin (Sn)
over Phosphor
Bronze, 18-24,
22+22 AWG, Reel
Mini-Fit Female 39000073
Crimp Terminal,
Selective Gold (Au)
and Selective Tin
(Sn) over Nickel (Ni),
18-24 AWG, Reel
Mini-Fit Male Crimp 39000075
Terminal, Brass,
Gold (Au) Contact
Plating, Lead-free,
18-24 AWG, Reel
Mini-Fit Male Crimp 39000120
Terminal, Tin
(Sn) Plated Brass
Contact, 18-24 AWG,
Reel
Mini-Fit Male Crimp 39000121
Terminal, Tin
(Sn) Plated Brass
Contact, 18-24 AWG,
Bag
Mini-Fit Male Crimp 39000126
Terminal, Tin (Sn),
Phosphor Bronze,
18-24 AWG, Reel
Mini-Fit Female 39000181
Crimp Terminal,
Selective Gold (Au)
over Phosphor
Bronze, 18-24 AWG,
Reel
Mini-Fit Female 39000207
Crimp Terminal, Tin
(Sn) over Nickel (Ni),
18-24 AWG, Reel
Mini-Fit Female 39000213
Crimp Terminal, Tin
(Sn) over Phosphor
Bronze, 18-24 AWG,
Reel
Mini-Fit Male Crimp 39000219
Terminal, Phosphor
Bronze, Gold (Au),
18-24 AWG, Reel
Mini-Fit Female 39000428
Crimp Terminal,

Selective Gold (Au)
and Selective Tin
(Sn) over Nickel (Ni),
18-24 AWG, Reel
Mini-Fit Male Crimp 39000430
Terminal, Brass,
Gold (Au) Contact
Plating, Lead-free,
18-24 AWG, Reel
Mini-Fit Plus Crimp 457501111
Terminal, 18-20
AWG, Reel, Copper
(Cu) Alloy, Tin (Sn)
Mini-Fit Plus Crimp 457501211
Terminal, 18-20
AWG, Reel, Copper
(Cu) Alloy, Gold (Au)
Selective
Mini-Fit Plus Crimp 460121141
Terminal, 18-20
AWG, Reel, Tin (Sn)
Plating
Mini-Fit Plus Crimp 460121241
Terminal, 18-20
AWG, Reel, 0.76µm
Selective Gold (Au)
Plating
Mini-Fit Plus High 460181541
Mating Cycle Female
Crimp Terminal,
18-20 AWG,
Reel, Select Gold
(Au) Plating with
Proprietary Molex
Advanced Contact
Surface Finish (CSF)
in Contact Area

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63902-3900](#)