

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0640016300](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Hand Crimp Tool

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)


General

Product Family	Application Tooling
Series	207129
Comments	Type RHT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	822350736947
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers
Application Tooling Documents

ATS-640016300-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[207129 Series](#)

Use With

Loose Piece Terminals

Application Tooling

Description

FAQ

Product #

InsulKrimp Fully [190130025](#)

Insulated Piggyback

Quick Disconnect,

Tab 6.35 x 0.81mm,

18-22 AWG, Red

Insulator, Loose

InsulKrimp Fully [190130026](#)

Insulated Piggyback

Quick Disconnect,

Tab 6.35 x 0.81mm,

18-22 AWG,

Expanded Red

Insulator, Mylar Tape

InsulKrimp Fully [190130027](#)

Insulated Piggyback

Quick Disconnect,

Tab 6.35 x 0.81mm,

18-22 AWG,
Expanded Red
Insulator Tape
InsulKrimp Fully 190130028
Insulated Piggyback
Quick Disconnect,
Tab 6.35 x 0.81mm,
18-22 AWG,
Expanded Flare, Red
Insulator, Tape
InsulKrimp Fully 190130029
Insulated Piggyback
Quick Disconnect,
Tab 6.35 x 0.81mm,
14-16 AWG, Blue
Insulator, Loose in a
bag
InsulKrimp Fully 190130030
Insulated Piggyback
Quick Disconnect,
Tab 6.35 x 0.81mm,
14-16 AWG,
Expanded Blue
Insulator, Tape
InsulKrimp Fully 190130031
Insulated Piggyback
Quick Disconnect,
Tab 6.35 x 0.81mm,
14-16 AWG,
Expanded Blue
Insulator, Loose
InsulKrimp Fully 190130032
Insulated Piggyback
Quick Disconnect,
Tab 6.35 x 0.81mm,
14-16 AWG, Blue
Insulator, Tape and
Reel

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64001-6300](#)