

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0640056200**
Status: **Active**
Overview: Application Tooling
Description: Air Powered Crimp Tool Head

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)


General

Product Family	Application Tooling
Series	<u>207129</u>
Comments	See Tooling Specification (PDF) Above. Type: AT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	<u>Application Tooling</u>
Product Name	N/A
Tool Type	Pneumatic Hand Tool
UPC	822350861069
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers
Application Tooling Documents

ATS-640056200-001, TM-192790001-001, TM-192790001SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Not Relevant

Not Contained

Search Parts in this Series

207129 Series

Use With

AT-200, 192790001 ATBA and Foot Switch, 190780307

Application Tooling | **FAQ**

Description	Product #
--------------------	------------------

InsulKrimp	<u>190110035</u>
------------	------------------

Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 18-22 AWG, Red Insulator, Loose

InsulKrimp	<u>190110037</u>
------------	------------------

Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 14-16 AWG, Blue Insulator, Loose

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64005-6200](#)