

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0640060200](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Manual Arbor Press, SC Power Connector


**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207125</a>
Function	Insulation Displacement (IDT)
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	N/A
Tool Type	Arbor Press
UPC	822348127054
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Material Info**

**Reference - Drawing Numbers**  
Application Tooling Documents [ATS-640060200-001](#)



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Not Reviewed

Not Reviewed

Not Reviewed

**Search Parts in this Series**

[207125 Series](#)

**Application Tooling** | **FAQ**  
**Description** | **Product #**

Self-Contained Power Connector for Solid Nonmetallic Sheathed Cable, 12-14 AWG	<a href="#">190451000</a>
Self-Contained Power Connector for Solid Nonmetallic Sheathed Cable, 12-14 AWG	<a href="#">194011000</a>
Self-Contained Tap Splice Connector for Solid Nonmetallic Sheathed Cable, 12-14 AWG	<a href="#">194021000</a>
Self-Contained Power Connector for 2 Circuit Round Cable with Ground, 14 AWG, Insulation Diameter 15.24mm	<a href="#">194030011</a>

Self-Contained Power Connector for Stranded Nonmetallic Sheathed Cable, 12 AWG	<u>194031010</u>
Self-Contained Power Connector for Stranded Nonmetallic Sheathed Cable, 14-16 AWG	<u>194031011</u>
Self-Contained Power Connector for Solid or Stranded Nonmetallic Sheathed Cable, 10 AWG	<u>194031300</u>
Self-Contained Power Connector for 2 Circuit Round Cable with Ground, 14 AWG, Insulation Diameter 8.64-11.18mm	<u>194031310</u>
Self-Contained Power Connector for 2 Circuit Round Cable with Ground, 12 AWG, Insulation Diameter 8.64-11.18mm	<u>194210001</u>
Self-Contained Power Connector for 2 Circuit Round Cable with Ground, 12 AWG, Insulation Diameter 15.24mm	<u>194210002</u>

This document was generated on 07/31/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64006-0200](#)