

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0640070100](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Crimp Head for the AT-200 Pneumatic Hand Tool

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207129</a>
Comments	Type: AT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	N/A
Tool Type	Pneumatic Hand Tool
UPC	756054575512
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Physical**


Net Weight 462.000/g

**Material Info**

Engineering Number AT-1992

**Reference - Drawing Numbers**

Application Tooling Documents  
ATS-640070100-001, TM-192790001-001, TM-192790001SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/30/2017 (7 July 2017)

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[207129 Series](#)

**Use With**

Molex AT-200 HandHeld Pneumatic Tool  
[192790001](#)

**Application Tooling**

**Description**

**FAQ**

**Product #**

Krimptite Quick Disconnect, Male, for 18-22 (0.80-0.35mm <sup>2</sup> ) Wire, Box, Tab 6.35 x 0.81mm	<a href="#">190220004</a>
Krimptite Quick Disconnect, Male, for 14-16 AWG Wire, Box	<a href="#">190220018</a>
Krimptite Snap Plug, for 18-22 AWG Wire	<a href="#">190330001</a>
Krimptite Snap Plug, for 18-22 AWG Wire	<a href="#">190330003</a>
Krimptite Ring Tongue Terminal for	<a href="#">190440168</a>

14-16 Heavy Duty  
AWG Wire  
Krimptite Ring 190440184  
Tongue Terminal for  
14-16 Heavy Duty  
AWG Wire  
Krimptite Ring 190440186  
Tongue Terminal for  
14-16 Heavy Duty  
AWG Wire  
RING VERSAKRIMP 190560083  
H/D (B-328-10HD)  
SPM  
Krimptite Ring 190690027  
Tongue Terminal for  
18-22 AWG Wire  
Krimptite Ring 190690029  
Tongue Terminal for  
18-22 AWG Wire  
Krimptite Ring 190690031  
Tongue Terminal for  
18-22 AWG Wire  
Krimptite Ring 190690033  
Tongue Terminal for  
18-22 AWG Wire  
Krimptite Ring 190690035  
Tongue Terminal for  
18-22 AWG Wire  
Krimptite Ring 190690037  
Tongue Terminal for  
18-22 AWG Wire  
Krimptite Ring 190690040  
Tongue Terminal for  
18-22 AWG Wire  
Krimptite Ring 190690042  
Tongue Terminal for  
18-22 AWG Wire  
Krimptite Ring 190690045  
Tongue Terminal for  
18-22 AWG Wire  
Krimptite Ring 190690049  
Tongue Terminal for  
18-22 AWG Wire  
Krimptite Ring 190690052  
Tongue Terminal for  
18-22 AWG Wire  
Krimptite Ring 190690054  
Tongue Terminal for  
18-22 AWG Wire  
Krimptite Ring 190690056  
Tongue Terminal for  
18-22 AWG Wire  
Krimptite Ring 190690061  
Tongue Terminal for  
18-22 AWG Wire  
Krimptite Ring 190690093  
Tongue Terminal for  
14-16 AWG Wire  
Krimptite Ring 190690096  
Tongue Terminal for  
14-16 AWG Wire  
Krimptite Ring 190690099  
Tongue Terminal for  
14-16 AWG Wire

Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690101</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690103</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690105</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690107</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690109</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690112</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690114</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690116</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690121</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690123</u>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 1/2" (M12), Length 32.51mm	<u>190690192</u>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 3/8" (M9), Length 32.51mm	<u>190690196</u>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 7/16" (M11), Length 32.51mm	<u>190690198</u>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 4 (M2.6), Length 19.94mm	<u>190690200</u>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 6 (M3.5), Length 19.94mm	<u>190690202</u>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 8 (M4), Length 19.94mm	<u>190690205</u>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire,	<u>190690209</u>

Stud Size 10 (M5),  
Length 19.94mm  
Krimptite Ring [190690217](#)  
Tongue Terminal for  
10-12 AWG Wire,  
Stud Size 10 (M5),  
Length 24.18mm  
Krimptite Ring [190690219](#)  
Tongue Terminal for  
10-12 AWG Wire,  
Stud Size 1/4" (M6),  
Length 24.18mm  
Krimptite Ring [190690223](#)  
Tongue Terminal for  
10-12 AWG Wire,  
Stud Size 5/16" (M8),  
Length 24.18mm  
Krimptite Ring [190690230](#)  
Tongue Terminal for  
10-12 AWG Wire,  
Stud Size 6 (M3.5),  
Length 18.82mm  
Krimptite Ring [190690233](#)  
Tongue Terminal for  
10-12 AWG Wire,  
Stud Size 8 (M4),  
Length 18.82mm  
Krimptite Ring [190690236](#)  
Tongue Terminal for  
10-12 AWG Wire  
Krimptite Ring [190690238](#)  
Tongue Terminal for  
10-12 AWG Wire,  
Stud Size 1/4" (M6),  
Length 26.82mm  
Krimptite Ring [190690241](#)  
Tongue Terminal for  
10-12 AWG Wire,  
Stud Size 3/8" (M9),  
Length 26.82mm  
Krimptite Ring [190690244](#)  
Tongue Terminal for  
10-12 AWG Wire,  
Stud Size 5/16" (M8),  
Length 26.82mm  
Krimptite Snap [190980017](#)  
Spade Terminal, for  
18-22 AWG Wire,  
Stud Size 5 (M3),  
14.86mm Length  
Krimptite Snap [190980018](#)  
Spade Terminal,  
for 18-22 AWG  
Wire, Stud Size 5-6  
(M3-3.5), 14.86mm  
Length  
Krimptite Snap [190980023](#)  
Spade Terminal, for  
18-22 AWG Wire,  
Stud Size 8 (M4),  
16.41mm Length  
Krimptite Snap [190980024](#)  
Spade Terminal, for  
18-22 AWG Wire,

Stud Size 10 (M5), 17.60mm Length Krimptite Snap	<u>190980041</u>
Spade Terminal, for 14-16 AWG Wire, Stud Size 5 (M3), 14.86mm Length Krimptite Snap	<u>190980043</u>
Spade Terminal, for 14-16 AWG Wire, Stud Size 5-6 (M3-3.5), 14.86mm Length Krimptite Snap	<u>190980047</u>
Spade Terminal, for 14-16 AWG Wire, Stud Size 8 (M4), 16.41mm Length Krimptite Snap	<u>190980049</u>
Spade Terminal, for 14-16 AWG Wire, Stud Size 10 (M5), 17.60mm Length Krimptite Snap	<u>190980069</u>
Spade Terminal, for 10-12 AWG Wire, Stud Size 5-6 (M3-3.5), 16.87mm Length Krimptite Snap	<u>190980074</u>
Spade Terminal, for 10-12 AWG Wire, Stud Size 10 (M5), 19.60mm Length Krimptite Flanged Spade Tongue	<u>191180021</u>
Terminal for 18-22 AWG Wire, Stud Size 6 (M3.5), Length 14.12mm Krimptite Flanged Spade Tongue	<u>191180025</u>
Terminal for 18-22 AWG Wire, Stud Size 10 (M5) Krimptite Flanged Spade Tongue	<u>191180080</u>
Terminal for 10-12 AWG Wire, Stud Size 8 (M4), Length 19.91mm Krimptite Flanged Spade Tongue	<u>191180082</u>
Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Length 19.91mm Krimptite Flanged Spade Tongue	<u>191180086</u>
Terminal for 10-12 AWG Wire, Stud Size 8 (M4), Length 19.56mm Krimptite Flanged Spade Tongue	<u>191180088</u>

Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Length 19.56mm	
Krimptite Block Spade Terminal for 10-12 AWG Wire	<u>191290005</u>
Krimptite Block Spade Terminal for 10-12 AWG Wire	<u>191290007</u>
Krimptite Block Spade Terminal for 10-12 AWG Wire	<u>191290008</u>
Krimptite Block Spade Terminal for 18-22 AWG Wire	<u>191290039</u>
Krimptite Block Spade Terminal for 18-22 AWG Wire	<u>191290041</u>
Krimptite Block Spade Terminal for 18-22 AWG Wire	<u>191290043</u>
Krimptite Block Spade Terminal for 18-22 AWG Wire	<u>191290045</u>
Krimptite Block Spade Terminal for 18-22 AWG Wire	<u>191290047</u>
Krimptite Block Spade Terminal for 18-22 AWG Wire	<u>191290053</u>
Krimptite Block Spade Terminal for 18-22 AWG Wire	<u>191290055</u>
Krimptite Spade Tongue Terminal for 18-22 AWG Wire, Non-Insulated, Stud Size 6	<u>191400035</u>
Krimptite Spade Tongue Terminal for 14-16 AWG Wire, Non-Insulated, Stud Size 6	<u>191400090</u>
Krimptite Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 6 (M3.5)	<u>191410020</u>
Krimptite Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 8 (M4)	<u>191410022</u>
Krimptite Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 10 (M5)	<u>191410024</u>
Krimptite Spade Tongue Terminal for 14-16 AWG Wire	<u>191410056</u>
Krimptite Spade Tongue Terminal for 14-16 AWG Wire	<u>191410058</u>
Krimptite Spade Tongue Terminal for 14-16 AWG Wire	<u>191410063</u>

Krimptite Spade Tongue Terminal for 14-16 AWG Wire	<u>191410065</u>
Krimptite Spade Tongue Terminal for 10-12 AWG Wire	<u>191410081</u>
Krimptite Spade Tongue Terminal for 10-12 AWG Wire	<u>191410083</u>
Krimptite Spade Tongue Terminal for 10-12 AWG Wire	<u>191410085</u>
VersaKrimp Block Spade Terminal for 18-22 AWG Wire	<u>191470019</u>
VersaKrimp Block Spade Terminal for 14-16 AWG Wire	<u>191470057</u>
VersaKrimp Block Spade Terminal for 14-16 AWG Wire	<u>191470062</u>
VersaKrimp Block Spade Terminal for 10-12 AWG Wire	<u>191470090</u>
VersaKrimp Spade Tongue Terminal for 10-12 AWG Wire	<u>191470096</u>
Krimptite Butt Splice for 10-12 AWG Wire	<u>191890015</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930007</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930009</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930014</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930016</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930023</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930041</u>
VersaKrimp Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 1/4" (M6)	<u>191930055</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930057</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930062</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930072</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930074</u>

VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930078</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930080</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930082</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930089</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930091</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930094</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930097</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930099</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930103</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930106</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire, Loose	<u>191930109</u>
METRIC RING VERSAKRIMP C-328-209 SPM	<u>191930112</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930116</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930120</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930128</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930130</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930134</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire, 3/8" (M9) Stud Size	<u>191930137</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930141</u>
RING VERSAKRIMP BENT (C-328-10R90)	<u>191930532</u>
VersaKrimp Temp- Term Ring Tongue Terminal for 14 to	<u>192030063</u>



16 AWG Wire, Stud  
Size 10 (M5)  
Krimptite Temp- 192030083  
Term Ring Tongue  
Terminal for 14 to  
16 AWG Wire, Stud  
Size 8 (M4)  
Krimptite Temp- 192030085  
Term Ring Tongue  
Terminal for 14 to  
16 AWG Wire, Stud  
Size 10 (M5)  
VersaKrimp Temp- 192030099  
Term Ring Tongue  
Terminal for 10 to  
12 AWG Wire, Stud  
Size 10 (M5)  
Krimptite Temp- 192030113  
Term Ring Tongue  
Terminal for 10 to  
12 AWG Wire, Stud  
Size 10 (M5)  
VersaKrimp Temp- 192030148  
Term Ring Tongue  
Terminal for 14 to  
16 AWG Wire, Stud  
Size 1/4" (M6)  
VersaKrimp Temp- 192030156  
Term Ring Tongue  
Terminal for 10 to  
12 AWG Wire, Stud  
Size 8 (M4)  
VersaKrimp Temp- 192030158  
Term Ring Tongue  
Terminal for 10 to  
12 AWG Wire, Stud  
Size 3/8" (M9)  
HI-TEMP PARALLEL 192030169  
SPLICE (C-T-303)  
VersaKrimp Temp- 192030182  
Term Ring Tongue  
Terminal for 10 to  
12 AWG Wire, Stud  
Size 1/4" (M6)  
Krimptite Temp-Term 192030386  
Butt Splice for 12-10  
AWG Wire, 483°C  
(900° F), Loose  
Piece  
VersaKrimp Parallel 192050001  
Splice for 14-16  
AWG Wire  
VersaKrimp Parallel 192050003  
Splice for 10-12  
AWG Wire  
VersaKrimp Parallel 192070001  
Splice for 18-22  
AWG Wire  
Krimptite Wire Pin 192110001  
Terminal for 12-10  
AWG Wire  
Krimptite Wire Pin 192110003  
Terminal for 22-18  
AWG Wire

Krimptite Wire Pin Terminal for 16-14 AWG Wire	<u>192110005</u>
VersaKrimp Butt Splice for 18-22 AWG Wire	<u>192150009</u>
Step Down Butt Splice for 14-22 AWG Wire	<u>192150013</u>
VersaKrimp Butt Splice for 14-16 AWG Wire	<u>192150018</u>
Step Down Butt Splice for 10-16 AWG Wire	<u>192150023</u>
VersaKrimp Butt Splice for 10-12 AWG Wire	<u>192150028</u>
VersaKrimp Metric Ring Terminal for M2.5 Stud Size (#4), Un-insulated	<u>193230001</u>
VersaKrimp Metric Ring Terminal for M3 Stud Size (#5), Un-insulated	<u>193230002</u>
VersaKrimp Metric Ring Terminal for M3-3.5 Stud Size (#5-#6), Un-insulated	<u>193230003</u>
VersaKrimp Metric Ring Terminal for M4 Stud Size (#8), Un-insulated	<u>193230004</u>
VersaKrimp Metric Ring Terminal for M5 Stud Size (#10), Un-insulated	<u>193230005</u>
VersaKrimp Metric Ring Terminal for M3 Stud Size (#5), Un-insulated	<u>193230006</u>
VersaKrimp Metric Ring Terminal for M3-3.5 Stud Size (#5-#6), Un-insulated	<u>193230007</u>
VersaKrimp Metric Ring Terminal for M4 Stud Size (#8), Un-insulated	<u>193230008</u>
VersaKrimp Metric Ring Terminal for M5 Stud Size (#10), Un-insulated	<u>193230009</u>
VersaKrimp Metric Ring Terminal for M6 Stud Size (1/4"), Un-insulated	<u>193230010</u>
VersaKrimp Metric Ring Terminal for M8 Stud Size (5/16"), Un-insulated	<u>193230011</u>
VersaKrimp Metric Ring Terminal for M4	<u>193230012</u>

Stud Size (#8), Un-  
insulated  
VersaKrimp Metric 193230013  
Ring Terminal for M3  
Stud Size (#5), Un-  
insulated  
VersaKrimp Metric 193230014  
Ring Terminal for M6  
Stud Size (1/4"), Un-  
insulated  
VersaKrimp Metric 193230015  
Ring Terminal for M8  
Stud Size (5/16"),  
Un-insulated  
VersaKrimp Metric 193230016  
Ring Terminal for  
M10 Stud Size  
(7/16"), Un-insulated

This document was generated on 08/23/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64007-0100](#)