

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0640074400](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Crimp Head for the AT-200 Pneumatic Hand Tool

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General


Product Family	Application Tooling
Series	207129
Comments	Type: AT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Air Tool
Tool Type	Pneumatic Hand Tool
UPC	822350644549
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number AT-1080

Reference - Drawing Numbers

Application Tooling Documents
ATS-640074400-001, TM-192790001-001, TM-192790001SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Not Relevant

Not Contained

Search Parts in this Series

[207129 Series](#)

Use With

Molex AT-200 HandHeld Pneumatic Tool
[192790001](#)

Application Tooling

Description

FAQ

Product #

VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 6 (M3.5)	191930143
VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 8 (M4)	191930146
VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 10 (M5)	191930149
VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6)	191930152

VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 5/16" (M8)	<u>191930157</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930159</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930163</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930167</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930171</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930179</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930184</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930186</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930187</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930192</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930195</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930198</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930200</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930202</u>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire	<u>191930204</u>
VersaKrimp Parallel Splice for 8 AWG Wire	<u>192050004</u>
VersaKrimp Butt Splice for 8 AWG Wire	<u>192150034</u>
Step Down Butt Splice for 8-12 AWG Wire	<u>192150037</u>

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64007-4400](#)