

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0640160038](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: ServiceGrade Hand Crimp Tool - Ratchet

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Comments	ServiceGrade crimp hand tools are low cost ratcheting hand tools used in field repair for a limited number of terminations. If a high quality tool is required or a higher volume of terminations required, please purchase the corresponding PremiumGrade crimp hand tool. A ServiceGrade crimp tool may or may not have a terminal locator and in some case may need the locator removed to operate properly. Type: SERV GRADE
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	ServiceGrade
Tool Type	Hand Crimp Tool
UPC	822348487790
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number 1992

Reference - Drawing Numbers

Application Tooling Documents [ATS-640160038-001](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[207129](#) Series

Use With

Krimptite/ VersaKrimp Quick Disconnects, Rings, Spades, Hooks, Block, and Flanged Spades, Butt and Parallel Splices, 10 - 22 AWG. The PremiumGrade Hand Tool for OEM Customers would be Part Number [640030100](#)

Application Tooling

Description

FAQ

Product #

Krimptite Quick Disconnect, Male, for 18-22 (0.80-0.35mm²) Wire, Box, Tab 6.35 x 0.81mm

[190220004](#)

Krimptite Quick Disconnect, Male, for 14-16 AWG Wire, Box

[190220018](#)

Krimptite Snap Plug, for 18-22 AWG Wire

[190330001](#)

Krimptite Snap Plug, 190330003
for 18-22 AWG Wire
Krimptite Ring 190440168
Tongue Terminal for
14-16 Heavy Duty
AWG Wire
Krimptite Ring 190440184
Tongue Terminal for
14-16 Heavy Duty
AWG Wire
Krimptite Ring 190440186
Tongue Terminal for
14-16 Heavy Duty
AWG Wire
RING VERSAKRIMP 190560083
H/D (B-328-10HD)
SPM
Krimptite Ring 190690027
Tongue Terminal for
18-22 AWG Wire
Krimptite Ring 190690029
Tongue Terminal for
18-22 AWG Wire
Krimptite Ring 190690031
Tongue Terminal for
18-22 AWG Wire
Krimptite Ring 190690033
Tongue Terminal for
18-22 AWG Wire
Krimptite Ring 190690035
Tongue Terminal for
18-22 AWG Wire
Krimptite Ring 190690037
Tongue Terminal for
18-22 AWG Wire
Krimptite Ring 190690040
Tongue Terminal for
18-22 AWG Wire
Krimptite Ring 190690042
Tongue Terminal for
18-22 AWG Wire
Krimptite Ring 190690045
Tongue Terminal for
18-22 AWG Wire
Krimptite Ring 190690049
Tongue Terminal for
18-22 AWG Wire
Krimptite Ring 190690052
Tongue Terminal for
18-22 AWG Wire
Krimptite Ring 190690054
Tongue Terminal for
18-22 AWG Wire
Krimptite Ring 190690056
Tongue Terminal for
18-22 AWG Wire
Krimptite Ring 190690061
Tongue Terminal for
18-22 AWG Wire
Krimptite Ring 190690093
Tongue Terminal for
14-16 AWG Wire
Krimptite Ring 190690096
Tongue Terminal for
14-16 AWG Wire

Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690099</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690101</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690103</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690105</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690107</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690109</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690112</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690114</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690116</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690121</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690123</u>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<u>190690192</u>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 1/2" (M12), Length 32.51mm	<u>190690196</u>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 3/8" (M9), Length 32.51mm	<u>190690198</u>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 7/16" (M11), Length 32.51mm	<u>190690198</u>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 4 (M2.6), Length 19.94mm	<u>190690200</u>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 6 (M3.5), Length 19.94mm	<u>190690202</u>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 8 (M4), Length 19.94mm	<u>190690205</u>

Krimptite Ring	<u>190690209</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Length 19.94mm	
Krimptite Ring	<u>190690217</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Length 24.18mm	
Krimptite Ring	<u>190690219</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 1/4" (M6), Length 24.18mm	
Krimptite Ring	<u>190690223</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 5/16" (M8), Length 24.18mm	
Krimptite Ring	<u>190690230</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 6 (M3.5), Length 18.82mm	
Krimptite Ring	<u>190690233</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 8 (M4), Length 18.82mm	
Krimptite Ring	<u>190690236</u>
Tongue Terminal for 10-12 AWG Wire	
Krimptite Ring	<u>190690238</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 1/4" (M6), Length 26.82mm	
Krimptite Ring	<u>190690241</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 3/8" (M9), Length 26.82mm	
Krimptite Ring	<u>190690244</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 5/16" (M8), Length 26.82mm	
Krimptite Snap	<u>190980017</u>
Spade Terminal, for 18-22 AWG Wire, Stud Size 5 (M3), 14.86mm Length	
Krimptite Snap	<u>190980018</u>
Spade Terminal, for 18-22 AWG Wire, Stud Size 5-6 (M3-3.5), 14.86mm Length	
Krimptite Snap	<u>190980023</u>
Spade Terminal, for 18-22 AWG Wire, Stud Size 8 (M4), 16.41mm Length	

Krimptite Snap Spade Terminal, for 18-22 AWG Wire, Stud Size 10 (M5), 17.60mm Length	<u>190980024</u>
Krimptite Snap Spade Terminal, for 14-16 AWG Wire, Stud Size 5 (M3), 14.86mm Length	<u>190980041</u>
Krimptite Snap Spade Terminal, for 14-16 AWG Wire, Stud Size 5-6 (M3-3.5), 14.86mm Length	<u>190980043</u>
Krimptite Snap Spade Terminal, for 14-16 AWG Wire, Stud Size 8 (M4), 16.41mm Length	<u>190980047</u>
Krimptite Snap Spade Terminal, for 14-16 AWG Wire, Stud Size 10 (M5), 17.60mm Length	<u>190980049</u>
Krimptite Snap Spade Terminal, for 10-12 AWG Wire, Stud Size 5-6 (M3-3.5), 16.87mm Length	<u>190980069</u>
Krimptite Snap Spade Terminal, for 10-12 AWG Wire, Stud Size 10 (M5), 19.60mm Length	<u>190980074</u>
Krimptite Flanged Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 6 (M3.5), Length 14.12mm	<u>191180021</u>
Krimptite Flanged Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 10 (M5)	<u>191180025</u>
Krimptite Flanged Spade Tongue Terminal for 10-12 AWG Wire, Stud Size 8 (M4), Length 19.91mm	<u>191180080</u>
Krimptite Flanged Spade Tongue Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Length 19.91mm	<u>191180082</u>
Krimptite Flanged Spade Tongue Terminal for 10-12 AWG Wire, Stud	<u>191180086</u>

Size 8 (M4), Length 19.56mm Krimptite Flanged Spade Tongue Terminal for 10-12 AWG Wire, Stud	<u>191180088</u>
Size 10 (M5), Length 19.56mm Krimptite Block Spade Terminal for 10-12 AWG Wire	<u>191290005</u>
Krimptite Block Spade Terminal for 10-12 AWG Wire	<u>191290007</u>
Krimptite Block Spade Terminal for 10-12 AWG Wire	<u>191290008</u>
Krimptite Block Spade Terminal for 18-22 AWG Wire	<u>191290039</u>
Krimptite Block Spade Terminal for 18-22 AWG Wire	<u>191290041</u>
Krimptite Block Spade Terminal for 18-22 AWG Wire	<u>191290043</u>
Krimptite Block Spade Terminal for 18-22 AWG Wire	<u>191290045</u>
Krimptite Block Spade Terminal for 18-22 AWG Wire	<u>191290047</u>
Krimptite Block Spade Terminal for 18-22 AWG Wire	<u>191290053</u>
Krimptite Block Spade Terminal for 18-22 AWG Wire	<u>191290055</u>
Krimptite Spade Tongue Terminal for 18-22 AWG Wire, Non-Insulated, Stud Size 6	<u>191400035</u>
Krimptite Spade Tongue Terminal for 14-16 AWG Wire, Non-Insulated, Stud Size 6	<u>191400090</u>
Krimptite Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 6 (M3.5)	<u>191410020</u>
Krimptite Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 8 (M4)	<u>191410022</u>
Krimptite Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 10 (M5)	<u>191410024</u>
Krimptite Spade Tongue Terminal for 14-16 AWG Wire	<u>191410056</u>

Krimptite Spade Tongue Terminal for 14-16 AWG Wire	<u>191410058</u>
Krimptite Spade Tongue Terminal for 14-16 AWG Wire	<u>191410063</u>
Krimptite Spade Tongue Terminal for 14-16 AWG Wire	<u>191410065</u>
Krimptite Spade Tongue Terminal for 10-12 AWG Wire	<u>191410081</u>
Krimptite Spade Tongue Terminal for 10-12 AWG Wire	<u>191410083</u>
Krimptite Spade Tongue Terminal for 10-12 AWG Wire	<u>191410085</u>
VersaKrimp Block Spade Terminal for 18-22 AWG Wire	<u>191470019</u>
VersaKrimp Block Spade Terminal for 14-16 AWG Wire	<u>191470057</u>
VersaKrimp Block Spade Terminal for 14-16 AWG Wire	<u>191470062</u>
VersaKrimp Block Spade Terminal for 10-12 AWG Wire	<u>191470090</u>
VersaKrimp Spade Tongue Terminal for 10-12 AWG Wire	<u>191470096</u>
Krimptite Butt Splice for 10-12 AWG Wire	<u>191890015</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930007</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930009</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930014</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930016</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930023</u>
VersaKrimp Ring Tongue Terminal for 18-22 AWG Wire	<u>191930041</u>
VersaKrimp Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 1/4" (M6)	<u>191930055</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930057</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930062</u>

VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930072</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930074</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930078</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930080</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930082</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930089</u>
VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire	<u>191930091</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930094</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930097</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930099</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930103</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930106</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire, Loose	<u>191930109</u>
METRIC RING VERSAKRIMP C-328-209 SPM	<u>191930112</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930116</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930120</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930128</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930130</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930134</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire, 3/8" (M9) Stud Size	<u>191930137</u>
VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire	<u>191930141</u>

RING VERSAKRIMP 191930532
BENT
(C-328-10R90)
VersaKrimp Temp- 192030063
Term Ring Tongue
Terminal for 14 to
16 AWG Wire, Stud
Size 10 (M5)
Krimptite Temp- 192030083
Term Ring Tongue
Terminal for 14 to
16 AWG Wire, Stud
Size 8 (M4)
Krimptite Temp- 192030085
Term Ring Tongue
Terminal for 14 to
16 AWG Wire, Stud
Size 10 (M5)
VersaKrimp Temp- 192030099
Term Ring Tongue
Terminal for 10 to
12 AWG Wire, Stud
Size 10 (M5)
Krimptite Temp- 192030113
Term Ring Tongue
Terminal for 10 to
12 AWG Wire, Stud
Size 10 (M5)
VersaKrimp Temp- 192030148
Term Ring Tongue
Terminal for 14 to
16 AWG Wire, Stud
Size 1/4" (M6)
VersaKrimp Temp- 192030156
Term Ring Tongue
Terminal for 10 to
12 AWG Wire, Stud
Size 8 (M4)
VersaKrimp Temp- 192030158
Term Ring Tongue
Terminal for 10 to
12 AWG Wire, Stud
Size 3/8" (M9)
HI-TEMP PARALLEL 192030169
SPLICE (C-T-303)
VersaKrimp Temp- 192030182
Term Ring Tongue
Terminal for 10 to
12 AWG Wire, Stud
Size 1/4" (M6)
Krimptite Temp-Term 192030386
Butt Splice for 12-10
AWG Wire, 483°C
(900° F), Loose
Piece
VersaKrimp Parallel 192050001
Splice for 14-16
AWG Wire
VersaKrimp Parallel 192050003
Splice for 10-12
AWG Wire
VersaKrimp Parallel 192070001
Splice for 18-22
AWG Wire

Krimptite Wire Pin Terminal for 12-10 AWG Wire	<u>192110001</u>
Krimptite Wire Pin Terminal for 22-18 AWG Wire	<u>192110003</u>
Krimptite Wire Pin Terminal for 16-14 AWG Wire	<u>192110005</u>
VersaKrimp Butt Splice for 18-22 AWG Wire	<u>192150009</u>
Step Down Butt Splice for 14-22 AWG Wire	<u>192150013</u>
VersaKrimp Butt Splice for 14-16 AWG Wire	<u>192150018</u>
Step Down Butt Splice for 10-16 AWG Wire	<u>192150023</u>
VersaKrimp Butt Splice for 10-12 AWG Wire	<u>192150028</u>
VersaKrimp Metric Ring Terminal for M2.5 Stud Size (#4), Un-insulated, Bag	<u>193230001</u>
VersaKrimp Metric Ring Terminal for M3 Stud Size (#5), Un-insulated, Bag	<u>193230002</u>
VersaKrimp Metric Ring Terminal for M3-3.5 Stud Size (#5-#6), Un-insulated, Bag	<u>193230003</u>
VersaKrimp Metric Ring Terminal for M4 Stud Size (#8), Un-insulated, Bag	<u>193230004</u>
VersaKrimp Metric Ring Terminal for M5 Stud Size (#10), Un-insulated, Bag	<u>193230005</u>
VersaKrimp Metric Ring Terminal for M3 Stud Size (#5), Un-insulated, Bag	<u>193230006</u>
VersaKrimp Metric Ring Terminal for M3-3.5 Stud Size (#5-#6), Un-insulated, Bag	<u>193230007</u>
VersaKrimp Metric Ring Terminal for M4 Stud Size (#8), Un-insulated, Bag	<u>193230008</u>
VersaKrimp Metric Ring Terminal for M5 Stud Size (#10), Un-insulated, Bag	<u>193230009</u>
VersaKrimp Metric Ring Terminal for M6	<u>193230010</u>

Stud Size (1/4"), Un-
insulated, Bag
VersaKrimp Metric 193230011
Ring Terminal for M8
Stud Size (5/16"),
Un-insulated, Bag
VersaKrimp Metric 193230012
Ring Terminal for M4
Stud Size (#8), Un-
insulated, Bag
VersaKrimp Metric 193230013
Ring Terminal for M3
Stud Size (#5), Un-
insulated, Bag
VersaKrimp Metric 193230014
Ring Terminal for M6
Stud Size (1/4"), Un-
insulated, Bag
VersaKrimp Metric 193230015
Ring Terminal for M8
Stud Size (5/16"),
Un-insulated, Bag
VersaKrimp Metric 193230016
Ring Terminal for
M10 Stud Size
(7/16"), Un-insulated,
Bag

This document was generated on 10/06/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64016-0038](#)