

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0714391364](#)  
**Status:** **Active**  
**Overview:** 1.00mm Mezzanine (IEEE 1386)  
**Description:** 1.00mm Mezz (IEEE 1386) Receptacle, Surface Mount, Dual Row, Vertical Stacking, Tube, 0.76µm Gold (Au), 64 Circuits Pick and Place Cap

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-70873-0607-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-70873-063-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	PCB Receptacles
Series	<a href="#">71439</a>
Application	Board-to-Board, Signal
Overview	<a href="#">1.00mm Mezzanine (IEEE 1386)</a>
Product Name	1.00mm Mezzanine (IEEE 1386)
UPC	800754687751

**Physical**

Circuits (Loaded)	64
Circuits (maximum)	64
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	Yes
Mated Height	12.00mm
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	1.270/g
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.762µm
Polarized to PCB	No
Robotic Placement	Pick and Place Cap
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-55° to +85°C
Termination Interface: Style	Surface Mount


**Electrical**

Current - Maximum per Contact	1.0A
Voltage - Maximum	100V

**Solder Process Data**

Duration at Max. Process Temperature (seconds)	040
Lead-free Process Capability	REFLOW
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

**Material Info**



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[71439 Series](#)

**Mates With**

[714361\\*\\*\\*](#) for Stack Height 11.00mm,  
[714362\\*\\*\\*](#) for Stack Height 12.00mm

**Reference - Drawing Numbers**

Packaging Specification

Sales Drawing

PK-70873-0607-001, PK-70873-063-001

714391000-000

This document was generated on 08/30/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[71439-1364](#)