

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0731160027](#)
Status: **Active**
Overview: RF Connectors and Microwave Products
Description: MCRF-to-Pigtail, 1.32mm Cable Diameter, Length 304.8mm, H25, 50 Ohms, One Piece Per Bag

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|------------------------|--|
| Product Family | Cable Assemblies |
| Series | 73116 |
| Assembly Configuration | Single Ended Connector |
| Connector to Connector | MCRF-to-Pigtail |
| Overview | RF Connectors and Microwave Products |
| Product Name | MCRF, RF |
| Type | RF Cable Assembly |
| UPC | 884982813564 |

Physical

| | |
|---------------------------|-----------------|
| Cable Length | 304.80mm (1.0') |
| Circuits (Loaded) | 0 |
| Gender | Plug-Pigtail |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Gold |
| Material - Resin | Polyester |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Single Ended | Yes |
| Wire/Cable Type | Coaxial |

Electrical

| | |
|-----------|-----|
| Impedance | 50Ω |
|-----------|-----|

Material Info

Reference - Drawing Numbers

| | |
|---------------|--------------|
| Sales Drawing | SD-73116-002 |
|---------------|--------------|



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[73116 Series](#)

Mates With

[734120110 MCRF, 50 Ohm, Receptacle](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[73116-0027](#)