

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0731160077](#)  
**Status:** **Active**  
**Overview:** RF Connectors and Microwave Products  
**Description:** MCRF-to-Pigtail, 0.81mm Cable Diameter, Length 304.8mm, H18, 50 Ohms, One Piece Per Bag

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	73116
Assembly Configuration	Single Ended Connector
Connector to Connector	MCRF-to-Pigtail
Overview	<a href="#">RF Connectors and Microwave Products</a>
Product Name	MCRF, RF
Type	RF Cable Assembly
UPC	884982813649

**Physical**

Cable Length	304.80mm (1.0')
Circuits (Loaded)	0
Gender	Plug-Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Resin	Polyester
Number of Rows	1
Packaging Type	Bag
Single Ended	Yes
Wire/Cable Type	Coaxial

**Electrical**

Impedance	50Ω
-----------	-----

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	SD-73116-007
---------------	--------------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[73116 Series](#)

**Mates With**

[734120110 MCRF, 50 Ohm, Receptacle](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[73116-0077](#)