

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0740990020](#)
Status: **Active**
Overview: [SL Modular Connectors](#)
Description: SL Wire-to-Board Header, Surface Mount, Single Row, Vertical, 3.05mm Pocket, Shrouded, 20 Circuits, Tin (Sn) Plating
Replacement Part Number : <http://www.molex.com/molex/search/partSearch?pQuery=&sType=p&query=17197300201719730020> (drop-in)

Documents:

3D Model	Product Specification PS-70541-001 (PDF)
3D Model (PDF)	Test Summary TS-70541-100-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-70400-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	74099
Application	Signal, Wire-to-Board
Overview	SL Modular Connectors
Product Name	SL
Replacement Part Number	1719730020 (drop-in)
UPC	756054760123


Physical

Breakaway	No
Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Black
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Capable	No
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.818/g
Number of Rows	1
Orientation	Vertical
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.54mm
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	Yes
Shrouded	Fully
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Solder Process Data



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[74099](#) Series

Mates With

SL Crimp Housing [70066](#) Option N, [70066](#) Option G, [70430](#) Option G, [70400](#) Option G

Lead-free Process Capability
Process Temperature max. C

REFLOW
235

Material Info

Reference - Drawing Numbers

Product Specification
Sales Drawing
Test Summary

PS-70400-001, PS-70541-001
SD-74099-001
TS-70541-100-001

This document was generated on 06/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74099-0020](#)