

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0783150011](#)

**Status:** **Active**

**Overview:** [DDR3 DIMM Sockets](#)

**Description:** 1.00mm Pitch Aerodynamic DDR3 DIMM Socket, Very Low Profile, Vertical, Press-Fit, with Pegs, Black Housing and Latches, 0.76µm Gold (Au Plating, 2.85mm Compliant Pin Length, 2.60mm PCB Thickness, 240 Circuits, Lead-Free

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-78315-001-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Application Specification AS-78315-001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR19980
UL	E29179

**Application tooling part link**

Application Tooling Part Link	62201-8656
Application Tooling Part Link	62202-3800

**General**

Product Family	Memory Module Sockets
Series	<a href="#">78315</a>
Component Type	Socket
JEDEC Outline	SO-012
Overview	<a href="#">DDR3 DIMM Sockets</a>
Product Name	DDR3 DIMM
UPC	884982126671

**Physical**

Circuits (Loaded)	240
Circuits (maximum)	240
Durability (mating cycles max)	25
Entry Angle	Vertical
Flammability	94V-0
Housing Color	Black
Keying to Mating Part	Yes
Latch Color	Black
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	7.595/g
PC Tail Length	2.85mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.762µm
Plating min - Termination	0.381µm
Temperature Range - Operating	-55° to +85°C
Termination Interface: Style	Through Hole - Compliant Pin

**Electrical**

Current - Maximum per Contact	1.0A
Voltage - Maximum	30V AC (RMS)/DC



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[78315 Series](#)

**Mates With**

JEDEC Standard 1.27mm Modules

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
DDR3 DIMM	<a href="#">622023800</a>
Memory Module	
Extraction Tool	

Voltage Key	Center
<b>Solder Process Data</b>	
Lead-freeProcess Capability	N/A
<b>Material Info</b>	
<b>Reference - Drawing Numbers</b>	
Application Specification	AS-78315-001-001
Product Specification	PS-78315-001-001
Sales Drawing	SD-78315-001-001

This document was generated on 01/10/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[78315-0011](#)