

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0797581009**  
**Status:** **Active**  
**Overview:** Off-the-Shelf Pre-Crimped Leads  
**Description:** Pre-Crimped Lead DuraClik Female-to-DuraClik Female, Tin (Sn) Plating, 300.00mm Length, 26 AWG, Black

**Documents:**

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<u>79758</u>
Application	Automotive
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	DuraClik Crimp Terminals
Overview	<u>Off-the-Shelf Pre-Crimped Leads</u>
Product Name	DuraClik
UPC	889056818599

**Physical**

Cable Length	300.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.743/g
Packaging Type	Bag
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Size AWG	26
Wire/Cable Type	UL 1061

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	2012341212-000
---------------	----------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contained Per -  
D(2021)4569-DC (8  
July 2021)  
reaction mass of  
2-ethylhexyl 10-  
ethyl-4,4-dioct  
Methylhexahydrophthalic  
anhydride  
Perfluorononan-1-  
oic acid  
(2,2,3,3,4,4,5,5,6,6,7  
Diocetyl tin dilaurate,  
stannane, dioctyl-,  
bis(co  
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o  
Pyrene  
Tris(4-nonylphenyl,  
branched and linear)  
phosphi  
Nonadecafluorodecanoic  
acid (PFDA) and its  
sodiu  
n-pentyl-  
isopentylphthalate  
Disodium-octaborate  
Phenol, 2-(2H-  
benzotriazol-2-yl)-4,6-  
bis(1,1-dim  
Ammonium-  
pentadecafluorooctanoate  
1,3-Propanesultone  
Dibutyltin-dichloride  
Decamethylcyclopentasiloxane  
bis(2-(2-  
methoxyethoxy)ethyl)  
ether  
Dipentyl phthalate  
Imidazolidine-2-thione  
Phenanthrene

**China RoHS**

Dicyclohexyl-  
phthalate  
4-aminoazobenzene  
Cyanamide, lead(2+)  
salt (1:1)  
Lead titanium  
zirconium oxide  
Dioxobis(stearato)trilead  
Lead-titanium-trioxide  
Lead oxide sulfate  
(Pb<sub>2</sub>O(SO<sub>4</sub>))  
Lead-dinitrate  
pyrochlore, antimony  
lead yellow  
Lead  
Lead(II,IV)-oxide  
Cadmium-sulphide  
Diboron-trioxide  
Decabromodiphenylether  
1,2-bis(2-  
methoxyethoxy)ethane  
1,2-Dimethoxyethane  
Boric acid, disodium  
salt, hydrate  
Bis(tributyltin) oxide  
Diarsenic-trioxide  
Diarsenic-pentaoxide  
Cobalt-dichloride

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[79758](#) Series

**Use With**

DuraClik Receptacle Housing [502351](#)

This document was generated on 08/27/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[79758-1009](#)