

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0847330005**
Status: **Active**
Overview: Sealed Industrial USB Solutions
Description: Sealed Industrial USB 3.0 Type A Receptacle-to-USB Type A Plug Dual-Ended Cordset, 1.31m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-84733-001-001 \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	84733
Assembly Configuration	Dual Ended Connectors
Comments	Fully shielded for EMI/RFI protection
Connector to Connector	USB Type A-to-A
Overview	Sealed Industrial USB Solutions
Product Name	Industrial USB
UPC	887191635514

Physical

Cable Length	1.31m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Female-Male
Material - Resin	PVC
Number of Rows	2
Packaging Type	Bag
Single Ended	No
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67, NEMA 6P
Wire Size AWG	N/A
Wire/Cable Type	USB

Electrical

Current - Maximum per Contact	1.0A
Impedance	Non-constant
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC (RMS)

Material Info

Reference - Drawing Numbers

Product Specification	PS-84733-001-001
Sales Drawing	SD-84733-001-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

84733 Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[84733-0005](#)