

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0848561204](#)
Status: **Active**
Overview: Brad Mini-Change Connectors
Description: Mini-Change Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 18 AWG, PVC Cable, 4.0m (13.12') Length, meets NMEA 2000

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	84856
Connector End A	Mini-Change
Connector End B	Mini-Change
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Mini-Change Connectors
Product Name	Mini-Change
Region	Europe
Type	Double Ended
UPC	822350909037

Physical

Cable Diameter	5.72mm (.225")
Cable Length	4.0m (13.12')
Color - Cable Jacket	Gray
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	18
Wire/Cable Type	Thick Standard Cable

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	300V

Material Info

Engineering Number	NMEA-DN11NB-M040
--------------------	------------------

Reference - Drawing Numbers

Sales Drawing	SD-84856-007
---------------	--------------



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[84856 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[84856-1204](#)