

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0875683063](#)
Status: **Active**
Overview: [Milli-Grid Connector System](#)
Description: [Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 30 Circuits, 0.38µm Gold \(Au\) Selective Plating, without Center Polarization Key and Locking Friction Ramp](#)

Documents:

[3D Model](#) [Application Specification 503940002-AS-000 \(PDF\)](#)
[3D Model \(PDF\)](#) [Packaging Specification PK-87568-0001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-87568-004-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family [IDT and Solder Connectors](#)
 Series [87568](#)
 Crimp Quality Equipment Yes
 Overview [Milli-Grid Connector System](#)
 Product Name [Milli-Grid](#)
 UPC [822348458035](#)
 Use With [875691030 Strain Relief \(Optional\)](#)

Physical

Circuits (Loaded) 30
 Circuits (maximum) 30
 Color - Resin Black
 Durability (mating cycles max) 100
 Flammability 94V-0
 Gender Female
 Glow-Wire Capable No
 Lock to Mating Part None
 Material - Metal Copper Alloy
 Material - Plating Mating Gold
 Material - Resin Polyester
 Net Weight 1.701/g
 Number of Rows 2
 Packaging Type Tray
 Panel Mount No
 Pitch - Mating Interface 2.00mm
 Polarized to Mating Part Yes
 Stackable No
 Temperature Range - Operating -20° to +85°C
 Termination Interface: Style IDT or Pierce
 Wire Size AWG 28

Electrical


Current - Maximum per Contact 1.0A
 Voltage - Maximum 125V

Solder Process Data

Lead-free Process Capability N/A

Material Info

Reference - Drawing Numbers



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2021)4569-DC (8
 July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[87568](#) Series

Mates With

[87831](#) Vertical PCB Header, [87832](#) Surface Mount PCB Header, [87833](#) Right Angle PCB Header

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
IDT - Manual - Handtool	621002000
Manual Press with IDT Ribbon Cable Tool Kit	621002200
IDT Ribbon Cable Adapter Kit for 2.00mm	621002400

Application Specification
Packaging Specification
Product Specification
Sales Drawing

503940002-AS-000
PK-87568-0001-001
PS-87568-004-001
SD-87568-003-001

IDT - Manual - Tool 621003200
Kit

This document was generated on 09/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[87568-3063](#)