

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0877620010](#)
Status: **Active**
Overview: [Milli-Grid Connector System](#)
Description: Milli-Grid Header, Dual Row Dual Body, Surface Mount, Vertical, 24 Circuits, 0.38µm Gold (Au) Selective Plating, 12.70mm Stacking Height, without Cap or Peg, Tray Packaging, Lead-Free

Documents:

Drawing (PDF)	Packaging Specification PK-89990-476-001 (PDF)
Product Specification PS-87761-100-001 (PDF)	Packaging Specification PK-89990-484-001 (PDF)
Application Specification 503940001-AS-000 (PDF)	Packaging Specification PK-89990-485-001 (PDF)
Packaging Specification PK-151033-0001-001 (PDF)	Packaging Specification PK-89990-487-001 (PDF)
Packaging Specification PK-87858-300-000 (PDF)	Test Summary 877610000-TS-000 (PDF)
Packaging Specification PK-89990-475-001 (PDF)	RoHS Certificate of Compliance (PDF)

General


Product Family	PCB Headers
Series	87762
Application	Board-to-Board, Signal
Overview	Milli-Grid Connector System
Product Name	Dual Body, Milli-Grid
UPC	756054908938

Physical

Breakaway	Yes
Circuits (Loaded)	26
Circuits (maximum)	26
Color - Resin	Black
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	7.90mm
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.170/g
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.381µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	125V



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[87762](#) Series

Mates With

[79107](#) Board-to-Board Top Entry Through Hole Receptacle, [79108](#) Board-to-Board FFC/FPC Top Entry Through Hole Receptacle, [79109](#) Board-to-Board Top/Bottom Entry SMT Receptacle, [87381](#) Board-to-Board Top Entry SMT Receptacle

Solder Process Data

Duration at Max. Process Temperature (seconds)	010
Lead-free Process Capability	REFLOW
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info**Reference - Drawing Numbers**

Application Specification	503940001-AS-000
Packaging Specification	PK-151033-0001-001, PK-87858-300-000, PK-89990-475-001, PK-89990-476-001, PK-89990-484-001, PK-89990-485-001, PK-89990-487-001
Product Specification	PS-87761-100-001
Sales Drawing	SD-87762-175-001
Test Summary	877610000-TS-000

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[87762-0010](#)