


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0901230124](#)
Status: **Active**
Overview: [C-Grid III Interconnects](#)
Description: 2.54mm Pitch C-Grid III Modular Crimp Housing Single Row, 2 Polarizing Buttons, 24 Circuits, Black

Documents:

3D Model	Application Specification 901190001-AS-000 (PDF)
Drawing (PDF)	Packaging Specification PK-90123-0001-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-99020-0001-001 (PDF)	



Series image - Reference only

Agency Certification

UL E29179

General

Product Family	Crimp Housings
Series	90123
Application	Signal, Wire-to-Board
Comments	2 Polarizing Buttons
Overview	C-Grid III Interconnects
Product Name	C-Grid III
UPC	800753705241

Physical

Circuits (maximum)	24
Color - Resin	Black
Flammability	94V-1
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	PPO
Net Weight	1.385/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	Yes
Temperature Range - Operating	-55° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	901190001-AS-000
Packaging Specification	PK-90123-0001-001
Product Specification	PS-99020-0001-001
Sales Drawing	SD-90123-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[90123 Series](#)

Mates With

C-Grid III Header [90120](#) , [90121](#) , C-Grid III Header [90136](#)

Use With

C-Grid III Crimp Terminal [90119](#)
 C-Grid III Pre-Crimped Lead [797582022](#) , [797582023](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[90123-0124](#)