


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0901361225](#)
Status: **Active**
Overview: [C-Grid III Interconnects](#)
Description: C-Grid III Header, Single Row, Vertical, Shrouded, 25 Circuits, 0.38µm Gold (Au) Selective Plating

Documents:

| | |
|---|--|
| 3D Model | Application Specification 901190001-AS-000 (PDF) |
| 3D Model (PDF) | Packaging Specification PK-90136-001-001 (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-99020-0001-001 (PDF) | |



Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|----------------|--|
| Product Family | PCB Headers |
| Series | 90136 |
| Application | Signal, Wire-to-Board |
| Overview | C-Grid III Interconnects |
| Product Name | C-Grid III |
| UPC | 800753673182 |

Physical

| | |
|--------------------------------|----------------|
| Breakaway | No |
| Circuits (Loaded) | 25 |
| Circuits (maximum) | 25 |
| Color - Resin | Black |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Material - Resin | Polyester |
| Net Weight | 3.484/g |
| Number of Rows | 1 |
| Orientation | Vertical |
| PC Tail Length | 2.90mm |
| PCB Locator | No |
| PCB Retention | None |
| PCB Thickness - Recommended | 1.60mm |
| Packaging Type | Tray |
| Pitch - Mating Interface | 2.54mm |
| Pitch - Termination Interface | 2.54mm |
| Plating min - Mating | 0.381µm |
| Plating min - Termination | 3.048µm |
| Polarized to PCB | No |
| Shrouded | Fully |
| Stackable | No |
| Temperature Range - Operating | -55° to +125°C |
| Termination Interface: Style | Through Hole |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[90136](#) Series

Mates With

[90123](#) C-Grid III Modular Crimp Housing,
[90156](#) C-Grid III Crimp Housing

Electrical

Current - Maximum per Contact 3.0A
Voltage - Maximum 350V AC/DC

Solder Process Data

Lead-freeProcess Capability WAVE

Material Info**Reference - Drawing Numbers**

Application Specification 901190001-AS-000
Packaging Specification PK-90136-001-001
Product Specification PS-99020-0001-001
Sales Drawing SDA-90136-001

This document was generated on 01/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[90136-1225](#)