

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0901512216](#)
Status: **Active**
Overview: [C-Grid Connector Products](#)
Description: C-Grid III PC Board Connector, Dual Row, Vertical, 16 Circuits, Gold (Au) Plating

Documents:

3D Model	Application Specification 713080001-AS-000 (PDF)
3D Model (PDF)	Application Specification 901190001-AS-000 (PDF)
Drawing (PDF)	Packaging Specification PK-90151-001-001 (PDF)
Product Specification PS-99020-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

General

Product Family	PCB Receptacles
Series	90151
Application	Board-to-Board, Signal
Overview	C-Grid Connector Products
Product Name	C-Grid
UPC	800753538955


Physical

Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94HB
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	1.367/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	2.90mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	3.048µm
Polarized to PCB	No
Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	3.0A
Grounding to PCB	No
Voltage - Maximum	350V

Solder Process Data



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Dipentyl phthalate
bis(2-(2-
methoxyethoxy)ethyl)
ether
Benzo(ghi)perylene
Octanoic acid,
2,2,3,3,4,4,5,5,6,6,7,7,8,8,8-
pen
Dodecamethylcyclotetrasiloxane
Decamethylcyclopentasiloxane
Octamethylcyclotetrasiloxane
1,2-diethoxyethane
Dibutyltin-dichloride
1,3-Propanesultone
C.I. Direct Black 38
Ammonium-
pentadecafluorooctanoate
2,4-Di-tert-butyl-6-(5-
chlorobenzotriazol-2-
yl)p
Disodium-octaborate
Dibutylbis(pentane-2,4-
dionato-O,O')tin
2-(2H-Benzotriazol-2-
yl)-4,6-
ditertpentylphenol
Terphenyl,
hydrogenated
1,2-
Benzenedicarboxylic
acid, dihexyl ester,
bra
diisohexyl phthalate
1,2-
Benzenedicarboxylic
acid, dipentyl ester, br

China RoHS

Lead-free Process Capability

WAVE

Material Info

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

713080001-AS-000, 901190001-AS-000

PK-90151-001-001

PS-99020-0001-001

SDA-90151-001

n-pentyl-
isopentylphthalate
Boric acid
Aluminosilicate
Refractory Ceramic
Fibres
Zirconia
Aluminosilicate
Refractory Ceramic
Fibr
Nonadecafluorodecanoic
acid (PFDA) and its
sodiu
Tris(4-nonylphenyl,
branched and linear)
phosphi
Perfluorobutane
sulfonic acid (PFBS)
and its sal
Fluoranthene
Pyrene
Dioctyltin dilaurate,
stannane, dioctyl-,
bis(co
Perfluorononan-1-
oic acid
(2,2,3,3,4,4,5,5,6,6,7
Methylhexahydrophthalic
anhydride
reaction mass of
2-ethylhexyl 10-
ethyl-4,4-dioct
Perfluorohexane-1-
sulphonic acid and its
salts
Lead chromate
Tris(2-chloroethyl)
phosphate
Boric acid, disodium
salt, hydrate
Strontium-chromate
1,2-
Benzenedicarboxylic
acid, di-C7-11-
branched
bis(2-methoxyethyl)
ether
1,2-
Benzenedicarboxylic
acid, bis(2-
methoxyethyl
1,2-Dimethoxyethane
1,2-bis(2-
methoxyethoxy)ethane
Decabromodiphenylether
Cadmium-oxide
Cadmium-sulphide
Lead
Cadmium
pyrochlore, antimony
lead yellow
Lead-dinitrate
Lead oxide sulfate
(Pb2O(SO4))
Lead-titanium-trioxide

Pentalead-tetraoxide-
sulphate
Trilead-dioxide-
phosphonate
Tetralead-trioxide-
sulphate
Dioxobis(stearato)trilead
Lead titanium
zirconium oxide
Cyanamide, lead(2+)
salt (1:1)
Cadmium Hydroxide
Sulfurous Acid, Lead
Salt, Dibasic
Silicic acid (H₂Si₂O₅),
barium salt (1:1),
lead-
[Phthalato(2-)]dioxotrilead
Fatty Acids, C16-18,
Lead Salts
N,N-
Dimethylformamide
Dicyclohexyl-
phthalate
Dihexyl-phthalate
Phenanthrene
Imidazolidine-2-thione

**Halogen-Free
Status**

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[90151](#) Series

Mates With

0.64mm square pins

This document was generated on 08/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[90151-2216](#)