

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936000014](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Metal Cable Gland - 5 Bar, for 5.00-12.00mm Cable, Pg13.5 Thread](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP68 - 5 Bar
IP Rating	IP68
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Cable Glands
Product Name	GWconnect
UPC	887191820965

Physical

Cable Diameter	5.00-12.00mm
Flammability	UL 94V-0
Material - Cable Gland	Brass
Material - Plating	Nickel
Net Weight	35.000/g
Packaging Type	Bag
Panel Cutout Diameter	20.70mm
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg13.5
Thread Type	(Pg)
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

Material Info

Engineering Number	7000.6826.0
--------------------	-------------

Reference - Drawing Numbers

Sales Drawing	936000014-000
---------------	---------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[93600 Series](#)

Use With

Industrial connector hoods and housings

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93600-0014](#)