

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936000035](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Plastic Cable Gland, with Washer and Gaskets, Pg11 Thread](#)

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP66 - Basic
Comments	3 Gaskets: 7.50, 10.00, and 12.50mm internal diameters.
IP Rating	IP66
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Cable Glands
Product Name	GWconnect
UPC	887191824376

Physical

Cable Diameter	7.00-12.00mm
Flammability	UL 94V-0
Gland Color	Light Grey RAL 7035
Material - Cable Gland	Polyamide
Material - Gasket	Elastomer
Material - Plating	Zinc (washer)
Material - Washer	Steel
Net Weight	10.000/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg11
Thread Type	(Pg)

Material Info

Engineering Number	7000.6837.0
--------------------	-------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93600 Series](#)

Use With

Plastic Enclosures Size 3A «21x21»

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93600-0035](#)