

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936000435](#)  
**Status:** **Active**  
**Overview:** [GWconnect Heavy Duty Connectors \(HDC\)](#)  
**Description:** [GWconnect Plastic Gable Gland, with Gasket, Pg42 Thread, Light Grey RAL 7035](#)

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93600</a>
Cable Gland Type	IP68 with Gasket
IP Rating	IP68
Overview	<a href="#">GWconnect Heavy Duty Connectors (HDC)</a>
Product Category	Cable Glands
Product Name	GWconnect
Standard	DIN 40430, EN 60529
UPC	887191857770

**Physical**

Cable Diameter	32.00-38.00mm
Flammability	UL 94V-2
Gland Color	Light Grey RAL 7035
Material - Cable Gland	Polyamide
Material - Gasket	NBR
Material - Nut	Polyamide
Net Weight	90.000/g
Packaging Type	Bag
Panel Cutout Diameter	54.50mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +100°C
Thread Size	Pg42
Thread Type	(Pg)
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

**Material Info**

Engineering Number	7000.7837.2
--------------------	-------------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[93600 Series](#)

**Use With**

Sealed Enclosures and Boxes

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93600-0435](#)